

PHILIPS

Straightener

220°C

Ceramic



HP8331



Perfect results for shorter styles

SalonStraight Precision

Unique design for detailed styling. Perfect for shorter or layered hair, the SalonStraight Detailer offers ceramic straightening plates plus a professional styling temperature of 220°C.

Beautifully styled hair

- Ceramic plates for smooth gliding and shiny hair
- Unique ultra slim design for detailed styling
- 200°C professional high heat for perfect salon results

Less hair damage

- Rounded plates to prevent hair trapping

Time saving

- Instant heat: Ready to use within 30 seconds

Ease of use

- Protective sleeve
- On/off switch
- Swivel cord to prevent tangled wires
- Dual voltage for worldwide use
- On/off indication light
- 1.8 m power cord

Specifications

Technical specifications

Voltage: 110–127 V

Wattage: 25 W

Cord length: 1,8 m

Serviceability

Replacement

Hair type

Current hair style: Straight, Wavy, Curly

End result: Straight

For fragile hair

Hair length: Short

Hair thickness: Thin, Thick

