

# PHILIPS

## Straightener

Care

Ceramic

HP8341/07



## Sleek and healthy shine

### Care Ceramic

The ceramic plates and ionic conditioning create a naturally sleek and healthy shine.

#### Beautifully styled hair

- Ceramic plates for smooth gliding and shiny hair
- Ion Conditioning for shiny, frizz-free hair
- 230°C professional high heat for perfect salon results

#### Less hair damage

- EHD+ technology for more protection and shinier results

#### Ease of use

- Digital settings with adjustable heat to get smooth results
- Fast heat up time, ready to use in 30 seconds
- Automatic shut-off after 1 hour
- Easy lock for convenient storage
- Including glamorous pouch for easy storage
- Swivel cord to prevent tangled wires
- Easy storage hook for convenient storage
- 2 m cord for ease of use

# Highlights

## 230°C professional temperature



This high temperature enables you change the shape of your hair, and gives you that perfect look, as if you've just come from the salon.

## Ceramic plates



Ceramic is microscopically smooth and durable by nature, and is therefore one of the best materials for straightening plates. The plates glide effortlessly through your hair, giving you perfect shiny hair.

## Ion Conditioning




Ion Conditioning for shiny, frizz-free hair

## Digital settings



Digital settings with adjustable heat to get smooth results with all hair types

## EHD+ technology



Advanced Philips EHD+ technology means that your styler will always distribute the heat very evenly - even at high temperatures, and prevents damaging hot spots. This gives added protection and thus helps to keep your hair healthy and shiny.

## Instant heat up



The straightener has a fast heat up time, being ready to use in 30 seconds

## Automatic shut-off after 1 hour



Automatic shut-off after 1 hour

## Easy lock

Easy lock for convenient storage

## Including glamorous pouch

Including glamorous pouch for easy storage

## Swivel cord

Useful swivel cord technology rotates the cord to prevent tangled wires.

## Easy storage hook



The rubberised hook is located at the base of the handle and provides another storage option, particularly convenient for use in the home or when staying at a hotel.

## 2 m cord



The long cord gives you maximum flexibility.

# Specifications

## Technical specifications

Voltage: 110-240 V

Heating time: 30 s

Heater type: PTC

Maximum temperature: 230 °C

## Features

Ready for use indicator

Heater type: PTC

Swivel cord

Ceramic coating

## Hair type

End result: Straight

Hair length: Long, Medium, Short

Hair thickness: Medium, Thick, Thin

## Service

2-year worldwide guarantee

