

PHILIPS

Straightener

SalonStraight

Respect



HP8342



Respect your hair day and night

SalonStraight Respect

Philips offers you the unique Care Touch[®] setting to maintain your straight style for longer with less damage.

Beautifully styled hair

- Ceramic plates for smooth gliding and shiny hair
- Ion Conditioning for shiny, frizz-free hair
- 230°C professional high heat for perfect salon results

Less hair damage

- Healthier restyling with auto-settings to gentler temperature
- EHD+ technology for more protection and shinier results

Ease of use

- Digital settings with adjustable heat to get smooth results
- Fast heat up time, ready to use in 30 seconds
- Automatic shut-off after 1 hour
- Easy lock for convenient storage
- Including glamorous pouch for easy storage
- Swivel cord to prevent tangled wires
- 2 m cord for ease of use

Highlights

Style refresh



Automatic setting for healthy restyling. Maintain your style all day, while respecting the quality of your hair

Ion Conditioning




Ion Conditioning for shiny, frizz-free hair

Digital settings



Digital settings with adjustable heat to get smooth results with all hair types

EHD+ technology



Advanced Philips EHD+ technology means that your styler will always distribute the heat very evenly - even at high temperatures, and prevents damaging hot spots. This gives added protection and thus helps to keep your hair healthy and shiny.

Instant heat up



The straightener has a fast heat up time, being ready to use in 30 seconds

Automatic shut-off after 1 hour



Automatic shut-off after 1 hour

Easy lock

Easy lock for convenient storage

Including glamorous pouch

Including glamorous pouch for easy storage

Swivel cord

Useful swivel cord technology rotates the cord to prevent tangled wires.

2 m cord



The long cord gives you maximum flexibility.

230°C professional temperature



This high temperature enables you change the shape of your hair, and gives you that perfect look, as if you've just come from the salon.

Specifications

Technical specifications

Voltage: 110-240 V

Heating time: 30 s

Heater type: PTC

Maximum temperature: 230 °C

Features

Ready for use indicator

Swivel cord

Ceramic coating

Hair type

End result: Straight

Hair length: Long, Medium, Short

Hair thickness: Medium, Thick, Thin

Service

2-year worldwide guarantee

