

PHILIPS

Straightener

MoistureProtect

MoistureProtect technology

Ionic

Floating ceramic plates



HP8372/00



Preserve your hair's natural hydration For a healthy shine

Sensor technology protects the moisture balance of your hair. The sensor diagnoses your hair 30 times per second and adapts the temperature to preserve natural hydration. Up to 63% moisture preservation (measured after 1 stroke in 2013).

MoistureProtect technology

- Perfect moisture protection with innovative sensor

Beautifully styled hair

- Prevents static for smooth, frizz free shiny hair

Ease of use


- Instant heat-up time of 15secs
- Faster, more caring high-performance heater
- 3 digital temperature settings

Caring technology

- Apply less pressure to hair to reduce the risk of breakage
- Perfect heat control with innovative sensor


Highlights

MoistureProtect technology




The sensor diagnoses your hair 30 times per second and adapts the temperature to preserve natural hydration of your hair.

Ionic conditioning



Charged negative ions eliminate static, condition the hair and smooth down the hair cuticles to intensify the hair's shine and glossiness. The result is hair that is smooth, shiny and frizz-free.

Floating ceramic plates



The floating plates move to adjust the pressure on the hair. This protects the hair shaft from being damaged and reduces the possibility of hair breakage.

MoistureProtect sensor



MoistureProtect sensor regulates the heat of the straightening plates for your hair needs, protecting the hair from overheating.


High-performance heater



This straightener keeps a more constant temperature for consistent results. Its high performance heater provides a more caring


temperature while getting the exact style you want! Styling will be faster, since you need less strokes, while straightening.

15 sec. heat-up time



The high-performance heater ensures a fast heat-up time of just 15 seconds.

Temperature control



3 temperature settings (200 - 175 - 150 Celsius) that work together with the sensor to ensure that you always straighten at the best temperature for your hair type.

Specifications

Technical specifications

Cord length: 2.0 m

Heat-up time: 15 sec

Maximum temperature: 200 °C

Heater Type: High-performance heater

Voltage: 110-240V

Caring technologies

MoistureProtect technology

Floating ceramic plates

Ionic

Features

Ceramic coating

Auto shut-off: after 60 min

Swivel cord

Hidden display

Service

2-year worldwide guarantee

Accessories

Pouch

