

Hair Straightener

- MoistureProtect technology
- Ionic
- Floating ceramic plates

HP8372/03

Preserve your hair's natural hydration

For a healthy shine

The sensor technology in our MoistureProtect Hair Straightener protects the moisture balance of your hair. The sensor diagnoses your hair 30 times per second and adapts the temperature to preserve natural hydration.

Benefits

Beautifully styled hair

- Prevents static for smooth, frizz-free, shiny hair

Ease of use

- Fast heat-up time of 15 secs
- Fast, high-performance heater
- 3 digital temperature settings

Caring technology

- Apply less pressure to hair to reduce the risk of breakage
- Perfect heat control with innovative sensor

MoistureProtect technology


- Perfect moisture protection with innovative sensor

PHILIPS

MoistureProtect

Features

15-sec. heat-up time



The high-performance heater ensures a fast heat-up time of just 15 seconds.

Floating ceramic plates



The floating plates move to adjust the pressure on the hair. This protects the hair shaft from being damaged and reduces the possibility of hair breakage.

High-performance heater



This hair straightener keeps a more constant temperature for consistent results. Styling will be faster, as you need fewer strokes while straightening.

Ionic conditioning




Charged negative ions eliminate static, condition the hair and smooth down the hair cuticles to intensify the hair's shine and glossiness. The result is hair that is smooth, shiny and frizz-free.

MoistureProtect sensor




MoistureProtect sensor regulates the heat of the straightening plates for your hair needs, protecting the hair from overheating.

MoistureProtect technology



The sensor diagnoses your hair 30 times per second and adapts the temperature to preserve your hair's natural hydration.

Temperature control



3 temperature settings (200 - 175 - 150 Celsius) that work together with the sensor to ensure that you always straighten at the best temperature for your hair type.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Technical specifications

Cord length	2.0 m
Heat-up time	15 sec
Maximum temperature	200 °C
Heater Type	High-performance heater
Voltage	110-240V

Caring technologies

MoistureProtect technology	Yes
Floating ceramic plates	Yes
Ionic	Yes

Features

Ceramic coating	YES
Auto shut-off	after 60 min
Hanging loop	Yes
Swivel cord	Yes
Hidden display	YES

Service

2-year worldwide guarantee	Yes
----------------------------	-----

Accessories

Pouch	YES
-------	-----

MoistureProtect

Packaging dimensions

Height	6.30 cm
Width	38.50 cm
Depth	12.20 cm
Net weight	0.44 kg
Gross weight	0.66 kg
EAN	08710103667551
Number of products included	1
Country of origin	CN
Harmonised Systems Code	851632

Outer Carton

Length	40.00 cm
Width	25.70 cm
Height	21.30 cm
Gross weight	4.32 kg
EAN	18710103667558
Number of consumer packages	6



data subject to change
2019, May 24

Version: 3.1.1
EAN: 08710103667551

© 2019 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com