

Philips
Curling iron

32 mm tong
Ceramic

HP8600



Natural bouncy curls in an easy way

SimplySalon Curl

Natural bouncy curls in an easy way. Get exactly the natural curly look you want with the SimplySalonCurl. A 32mm curling tong and professional ceramic coating sets this curler apart from the rest.

Beautifully styled hair

- 180°C temperature for beautiful results
- 32mm tong for beautiful curls and waves
- Ceramic Tourmaline for frizz-free curls and maximum shine

Time saving

- Instant heat: ready to use within 30 seconds

Ease of use

- Short curling clip for easy curl release
- Cool tip for easier and safer use
- On/off switch
- Easy storage hook for convenient storage
- Swivel cord to prevent tangled wires
- Dual voltage for worldwide use
- Included: Heat resistant pouch
- On/off indication light

PHILIPS

Specifications

Technical specifications

- Maximum temperature: 180 °C

Serviceability

- Replacement

Hair type

- Current hair style: Straight, Wavy, Curly
- End result: Curly, Voluminous
- For fragile hair
- Hair length: Long
- Hair thickness: Thin



Issue date 2014-03-17

Version: 2.0.1

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com