

PHILIPS

Curler

CurlCeramic

16 mm



HP8602/03



Create your curls with care

Curling iron with ceramic coating

Vivid, bouncy curls and ringlets for a fun-looking and youthful style are now easy to achieve thanks to the new CurlCeramic curling iron with protective ceramic coating

Beautifully styled hair

- 16-mm barrel for vivid, bouncy curls
- 190°C top temperature for perfect styling results

Less hair damage

- Protective ceramic coating

Ease of use

- LED light tells you when the curler is ready to use
- Automatic shut-off after 60 min
- Cool tip for easier and safer use
- Safety stand for easy use
- 1.8 m power cord
- Universal voltage

Highlights

Vivid, bouncy curls




With a barrel diameter of 16 mm, you can create bouncy curls and ringlets that are full of life, giving you a fun-looking and youthful style.

Gentle on your hair



Protective ceramic coating ensures even heat distribution and less hair damage for shiny and soft hair.

190°C top temperature



Top temperature of 190°C guarantees optimal results, while minimising hair damage.

Safe usage



Some hair straighteners and curling irons have been equipped with an automatic shut-off feature. This feature has been designed to provide peace of mind. If left on, the appliance will automatically switch off after 60 min.

Ready-to-use indicator

The LED light stops blinking when the curler has heated up and is ready to use.

Cool tip



The tip of the styler is made from a special heat insulating material to keep it cool; you can safely hold it while you're styling for optimal ease of use.

Specifications

Technical specifications

Maximum temperature: 190 °C

Temperature range: one setting

Cord length: 1.8 m

Colour/finishing: black-white

Heater type: PTC

Heating time: 60s

Voltage: worldwide

Barrel diameter: 16 mm

Features

Ceramic coating

Ready for use indicator

Cool tip

Swivel cord

Hanging loop

Hair type

End result: Tight curls and ringlets

Hair length: Long, Medium

Hair thickness: Medium, Thick, Thin

Service

2-year worldwide guarantee

