

PHILIPS

Dryer & Straightener

Essential

Styling Kit



HP8643/46



Miss Fresher's Styling Kit

Miss Fresher's is the perfect hair styling kit for instant results and everyday use. Combine gentle drying and caring straightening to achieve the beautiful hair you desire with our easy to use combination pack!

Beautifully styled hair

- Straightener: 210°C professional styling temperature
- Dryer: gentle drying power of 1000W for beautiful results
- Dryer: narrow concentrator for focused airflow

Ease of use


- Straightener: Fast heat up time, ready to use in 60 seconds
- Straightener: The swivel cord prevents tangled wires
- Straightener: use anywhere with universal voltage
- Dryer: compact design for easy handling
- Dryer: Easy storage hook for convenient storage

Less hair damage

- Straightener: Ceramic plates for smooth and easy gliding

Highlights

210°C professional high heat



This high temperature enables you change the shape of your hair and gives you that perfect look like you've just come from the salon.

Swivel cord



The swivel cord technology conveniently rotates the cord and prevents unnecessary tangles

Compact design



Compact and ergonomic, this hairdryer benefits from a clever modern design. This results in a dryer that is light and easy to handle yet small enough to store virtually anywhere.

Ceramic plates




Ceramic plates for ultrasmooth gliding and more shine for your hair

Gentle drying power 1000W



This 1000W hairdryer creates the optimum level of airflow and gentle drying power for beautiful results every day.

Narrow concentrator



The concentrator works by focusing the airflow onto specific areas. This results in precise styling, great touch-ups, or finishing a style.

Instant heat-up



The straightener has a fast heat up time, being ready to use in 60 seconds.

Universal Voltage

This straightener is ready to use anywhere in the world and is compatible with 110-240 voltage.

Easy storage hook



The rubberised hook is located at the base of the handle and provides another storage option, particularly convenient for use at home or when staying at a hotel.

Specifications

Technical specifications

Maximum temperature: Straightener 210 °C

Heat-up time: Straightener: 60 seconds

Voltage: Straightener: worldwide

Voltage: Dryer: 220-240 V

Cord length: Straightener & Dryer 1.6 m

Wattage: Dryer 1000 W

Features

Ceramic coating: Straightener yes

Swivel cord: Straightener yes

Narrow Concentrator: Dryer yes

Storage hook: Dryer yes

Service

2-year guarantee

