

PHILIPS

Gift set

KeraShine Ionic

Dryer and straightener set



HP8646/10



The KeraShine gift set for silky smooth hair

This KeraShine gift set with a 1600W dryer and wide-plate straightener is specifically designed to give you the benefits of Keratin and extra shine in one set. Give yourself the style you desire while being gentle on your hair.

Beautifully styled hair

- Straightener: Keratin ceramic plates for extra shine
- Straightener: 210°C professional styling temperature
- Dryer: 1600W drying power for perfect salon results

Less hair damage

- Dryer: 6 speed / heat settings for full drying flexibility
- More care with ion conditioning for shiny, frizz-free hair
- Dryer: Gentle drying at thermoprotect temperature
- Dryer: Even Heat Distribution to limit hot spots

Easy to use

- Straightener: Fast heat up time, ready to use in 60 seconds
- Straightener: Extra wide plates for thick or long hair

Highlights

Keratin Infused Ceramic plates



The keratin-infused ceramic plates are carefully designed to enhance gliding and shine while you straighten your hair, giving you the silky smooth hair you desire.

Ionic Care



Give your hair instant care with ionic conditioning. Charged negative ions eliminate static, condition the hair, and smoothen the cuticles to enhance your overall shine. The result is hair that is extra smooth and shiny without frizz.

210°C professional high heat



This high temperature enables you to change the shape of your hair and gives you that perfect look like you've just come from the salon.

Instant heat-up




The straightener has a fast heat up time, being ready to use in 60 seconds.

Dryer: 6 heat/speed settings



6 heat/speed setting for full flexibility and gentle drying. Choose the temperature setting that you prefer for gentle drying to your hair.

Wide plates



These extra wide straightening plates have been designed specifically for thick or long hair. The increased plate width can straighten more hair in one go and will help to reduce the time required to style.

Dryer: 1600W drying power



1600W drying power for perfect salon and styling results

ThermoProtect temperature



The ThermoProtect temperature provides the optimal drying temperature and gives additional protection from overheating the hair. With the same powerful airflow, you will get the best results in a caring way.

Even Heat Distribution



Philips EHD technology uses a uniquely designed air outlet to ensure heat is always distributed evenly across your hair, even at high temperatures. This gives you ultimate protection from hot spots or having your hair overheat.

Specifications

Technical specifications

Voltage: Straightener Worldwide V

Wattage: Dryer 1600 W

Heat-up time: Straightener: 60 seconds

Cord length: Straightener 1.8m; Dryer 1.6 m

Maximum temperature: Straightener 210 °C

Wide Plates: Straightener 47x75mm

Features

Cool shot: Dryer Yes

Hanging loop: Dryer Yes

Swivel cord: Straightener Yes

Keratin ceramic coating

Plate lock: Straightener Yes

Even Heat Distribution: Dryer Yes

ThermoProtect temperature: Dryer Yes

Service

2-year worldwide guarantee

