

# PHILIPS

## Air Styler

## Essential

Keratin Ceramic coating

Ionic care

ThermoProtect temperature

HP8659/00



## Easy hairstyling with ionic care

Dry and style in one go. Philips Air Styler with Keratin ceramic and Ionic care - for naturally straight and beautifully smooth hair.

### Prevent damage

- Protective ceramic coating with Keratin infusion
- More Care with ion conditioning for shiny, frizz-free hair
- ThermoProtect temperature setting

### Beautifully styled hair


- Gentle, yet effective styling power
- Paddle Straightening Brush for naturally straight looks
- 2 heat & speed settings

### Easy to use

- 1.8 m cord for maximum flexibility
- Easy storage hook for convenient storage

# Highlights

## 650W



The Air Styler with 650W airflow for a gentle drying and styling. Achieve beautiful results every day.

## Keratin ceramic coating



The bristles with keratin-infused ceramic coating glide smoothly through your hair for naturally straight and shiny look.

## Ionic Care

Ionic conditioning enables anti-static drying. Charged negative ions eliminate static hair, condition the hair and smooth down the hair cuticles to intensify the hair's shine and glossiness. The result is smooth and frizz-free hair that shines beautifully.


## ThermoProtect temperature

The ThermoProtect temperature setting provides the optimal drying temperature and gives additional protection from overheating the hair. With the same powerful airflow, you will get the best results in a caring way.

## Paddle Straightening Brush


With the innovative Paddle Straightening Brush, attached to the handle, you can create beautiful naturally straight looking hair, without damage.

## 2 heat & speed settings



Two flexible heat and speed settings for easy styling.

## 1.8 m cord



1.8 m cord for maximum flexibility.

## Easy storage hook

The rubberised hook is located at the base of the handle and provides another storage option, particularly convenient for use in the home or when staying at a hotel.

# Specifications

## Caring technologies

Keratin infused coating  
Ion technology  
ThermoProtect

## Power

Wattage: 650W  
Voltage: 220-240V

## Technical specifications

Heat settings: 2

## Ease of use

Storage hook

## Service

2-year worldwide warranty

