

3 headers

Philishave range 2001



International range  
(note: not all models will be available in all countries)



QUADRA ACTION

REFLEX ACTION

	HQ 6894	HQ 6893	HQ 6890	HQ 6871	HQ 6852	HQ 6832	HQ 6466	HQ 6426	HQ 5866	HQ 5846	HQ 5826	HQ 5816
<b>Shaving system</b>												
Dual shaving heads (slots & holes)	●	●	●	●	●	●	●	●	-	-	-	-
Easy clean waterproof shaver	●	●	●	●	●	●	●	●	●	●	●	●
3D Contour following shaving system	●	●	●	●	●	●	●	●	-	-	-	-
Lift & cut	●	●	●	●	●	●	●	●	●	●	●	●
Individually floating heads	●	●	●	●	●	●	●	●	●	●	●	●
Silent power	●	●	●	●	●	●	●	●	●	●	●	●
Vibration free, rotating system	●	●	●	●	●	●	●	●	●	●	●	●
Long, omnidirectional slots	●	●	●	●	●	●	●	●	●	●	●	●
Hair collecting chamber	●	●	●	●	●	●	●	●	●	●	●	●
<b>Power system</b>												
Rechargeable/mains	●	●	●	●	●	●	-	-	●	●	●	●
Rechargeable	-	-	-	-	-	-	-	-	-	-	-	-
Mains	-	-	-	-	-	-	●	●	-	-	-	-
Charging time	1hr.	1hr.	1hr.	1hr.	1 hr.	1 hr.	-	-	1hr.	1hr.	1hr.	1 hr.
Cordless shaving time up to	70'	70'	70'	70'	70'	70'	-	-	70'	70'	70'	30'
NiMh 'Green Energy' cell	2	2	2	2	2	2	-	-	2	2	2	1
Automatic voltage selection	●	●	●	●	●	●	●	●	●	●	●	●
12 Volts charging	●	●	●	●	●	●	-	-	-	-	-	-
<b>Luxury level</b>												
Charging indication	●	●	●	●	●	●	-	-	●	●	●	●
Battery full indication	●	●	●	●	●	●	-	-	●	●	●	●
Battery low indication	●	●	●	●	●	●	-	-	●	●	●	●
5 Segment charge cap. indication	LCD	LCD	LCD	LED's	-	-	-	-	LCD	LED's	-	-
Minutes left indication	●	●	●	-	-	-	-	-	-	-	-	-
Cleaning advice	●	●	●	-	-	-	-	-	-	-	-	-
Soft rubber grip panel	●	●	●	●	●	●	●	●	●	●	●	●
Metallic lacquer	-	●	-	●	-	-	●	-	●	-	-	-
Dual metallic lacquer	●	-	-	-	-	-	-	-	-	-	-	-
Trimmer	●	●	●	●	●	●	●	●	●	●	●	●
Electronic on/off switch	●	●	●	●	●	●	●	●	●	●	●	●
Deluxe storage cassette	●	●	●	●	-	-	●	-	●	-	-	-
Deluxe pouch	-	-	-	-	●	-	-	-	-	●	●	-
Regular pouch	-	-	-	-	-	●	-	-	-	-	-	●
Stand/wall holder	●	●	●	-	-	-	-	-	-	-	-	-
<b>Packaging</b>												
Dimensions fancy box (mm.)	134 x 108 x 189	134 x 108 x 189	134 x 108 x 189	134 x 92 x 189	134 x 92 x 189	134 x 92 x 189	134 x 92 x 189	134 x 92 x 189	134x71x189	134x71x189	134x71x189	134x71x189
Weight fancy box	590 gr.	590 gr.	590 gr.	560 gr.	460 gr.	456 gr.	435 gr.	430 gr.	463 gr.	401 gr.	397 gr.	364gr.
Dimensions master carton	276 x 226 x 205	276 x 226 x 205	276 x 226 x 205	381 x 199 x 148	381 x 199 x 148	381 x 199 x 148	381 x 199 x 148	381 x 199 x 148	222x199x282	222x199x282	222x199x282	222x199x282
Weight master carton	2620 gr.	2620 gr.	2620 gr.	2440 gr.	2380 gr.	2304 gr.	2230 gr.	2200 gr.	3000 gr.	2630 gr.	2600 gr.	2400 gr.
Master carton contains	4 pcs.	4 pcs.	4 pcs.	4 pcs.	4 pcs.	4 pcs.	4 pcs.	4 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.





## REFLEX ACTION

HQ 5806 HQ 5800 HQ 54 61 HQ 5421 HQ 5401

### Shaving system

Dual shaving heads (slots & holes)	-	-	-	-	-
Easy clean waterproof shaver	-	-	-	-	-
3D Contour following shaving system	●	●	●	●	●
Lift & cut	●	●	●	●	●
Individually floating heads	●	●	●	●	●
Silent power	●	●	●	●	●
Vibration free, rotating system	●	●	●	●	●
Long, omnidirectional slots	●	●	●	●	●
Hair collecting chamber	●	●	●	●	●

### Power system

Rechargeable/mains	●	●	-	-	-
Rechargeable	-	-	-	-	-
Mains	-	-	●	●	●
Charging time	1hr.	16hr.	-	-	-
Cordless shaving time up to	30'	30'	-	-	-
NiMh 'Green Energy' cell	1	1	-	-	-
Automatic voltage selection	●	●	●	●	●
12 Volts charging	-	-	-	-	-

### Luxury level

Charging indication	●	●	-	-	-
Battery full indication	●	-	-	-	-
Battery low indication	-	-	-	-	-
5 Segment charge cap. indication	-	-	-	-	-
Minutes left indication	-	-	-	-	-
Cleaning advice	-	-	-	-	-
Soft rubber grip panel	-	-	-	-	-
Metallic lacquer	-	-	●	-	-
Dual metallic lacquer	-	-	-	-	-
Trimmer	●	●	●	●	●
Electronic on/off switch	-	-	-	-	-
Deluxe storage cassette	-	-	●	-	-
Deluxe pouch	-	-	-	●	-
Regular pouch	●	●	-	-	●
Stand/wall holder	-	-	-	-	-

### Packaging

Dimensions fancy box (mm.)	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189
Weight fancy box	371 gr.	369 gr.	398 gr.	337 gr.	338 gr.
Dimensions master carton	222x199x282	222x199x282	222x199x282	222x199x282	222x199x282
Weight master carton	2450 gr.	2430 gr.	2610 gr.	2240 gr.	2290 gr.
Master carton contains	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.



## MICRO ACTION

HQ 4866 HQ 4856 HQ 4846 HQ 4826 HQ 4806 HQ 4601 HQ 4441 HQ 4421 HQ 4411 HQ 4401

### Shaving system

Dual shaving heads (slots & holes)	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Easy clean waterproof shaver	-	-	-	-	-	-	-	-	-	-	-	-	-	-
3D Contour following shaving syst	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Lift & cut	●	●	●	●	●	●	●	●	●	●	●	●	●	●
Individually floating heads	●	●	●	●	●	●	●	●	●	●	●	●	●	●
Micro groove	●	●	●	●	●	●	●	●	●	●	●	●	●	●
Silent power	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Vibration free, rotating system	●	●	●	●	●	●	●	●	●	●	●	●	●	●
Long, omnidirectional slots	●	●	●	●	●	●	●	●	●	●	●	●	●	●
Hair collecting chamber	●	●	●	●	●	●	●	●	●	●	●	●	●	●

### Power system

Rechargeable/mains	●	●	●	●	●	-	-	-	-	-	-	-	-	-
Rechargeable	-	-	-	-	-	-	●	-	-	-	-	-	-	-
Mains	-	-	-	-	-	-	-	●	-	-	-	-	-	-
Charging time	1hr.	1hr.	1hr.	8hr.	16hr.	16hr.	-	-	-	-	-	-	-	-
Cordless shaving time	70'	30'	30'	30'	30'	30'	-	-	-	-	-	-	-	-
NiMh 'Green Energy' cell	2	1	1	1	1	1*	-	-	-	-	-	-	-	-
Automatic voltage selection	●	●	●	●	●	●	-	-	-	-	-	-	-	-
Manual voltage selection	-	-	-	-	-	-	●	-	-	-	-	-	-	-
12 Volts charging	-	-	-	-	-	-	-	-	-	-	-	-	-	-

### Luxury level

Charging indication	●	●	●	●	●	●	-	-	-	-	-	-	-	-
Battery full indication	●	●	●	-	-	-	-	-	-	-	-	-	-	-
Battery low indication	●	●	-	-	-	-	-	-	-	-	-	-	-	-
5 Segment charge cap. indication	LED's	-	-	-	-	-	-	-	-	-	-	-	-	-
Minutes left indication	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Cleaning advice	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Soft rubber panels	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Metallic lacquer	●	●	-	-	-	-	-	-	●	-	-	-	-	-
Dual metallic lacquer	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Trimmer	●	●	●	●	●	●	-	-	-	-	-	-	-	●
Electronic on/off switch	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Deluxe storage cassette	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Deluxe pouch	●	-	-	-	-	-	-	-	●	-	-	-	-	-
Regular pouch	-	●	●	●	●	●	-	-	-	●	-	-	●	-
Stand/wall holder	-	-	-	-	-	-	-	-	-	-	-	-	-	-

### Packaging

Dimensions fancy box (mm.)	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189
Weight fancy box	456 gr.	443 gr.	465 gr.	413 gr.	435 gr.	467 gr.	410 gr.	410 gr.	410 gr.	410 gr.	410 gr.	410 gr.	410 gr.	400 gr.
Dimensions master carton	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282
Weight master carton	3010 gr.	2880 gr.	3010 gr.	2720 gr.	2830 gr.	3020 gr.	2680 gr.	2680 gr.	2680 gr.	2680 gr.	2680 gr.	2680 gr.	2680 gr.	2620 gr.
Master carton contains	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.	6 pcs.

\*NiCD cell