

PHILIPS

Dry electric shaver

Shaver series 3000

CloseCut heads Flex & Float

35+ mins' cordless use/1-hr charge

Pop-up trimmer

HQ6990/16



Close even on the neck

Lift&Cut blades

A close and comfortable shave for an affordable price. The Flex & Float system is combined with Lift & Cut blades, guaranteeing a close and comfortable shave.

Comfortably close

- Lift and Cut blades lift hairs to cut for a close shave

Adjusts to every curve of your face and neck

- Flex & Float adjusts to face and neck curves

Easy to use

- 2 year guarantee, worldwide voltage and replaceable blades
- Can be used corded and cordless
- 35+ shaving minutes, 1-hour charge
- Perfect for trimming your sideburns and moustache
- Charging indicator

Moustache and sideburn trimming

- Pop-up trimmer

Easy grip

- Ergonomically designed grip for easy handling



asimpleswitch.com

Highlights

Lift & Cut blades

The Lift & Cut dual blade system lifts hairs to cut comfortably

Flex and Float

Automatically adjusts to every curve of your face and neck for a smoother shave

35+ shaving minutes

You'll have 35+ minutes of shaving time—that's around 14 shaves—after 1 hour of charging. Plug it in for 3 minutes and you'll have enough power for one shave.

Corded and cordless use

Can be used corded and cordless

Pop-up trimmer

Complete your look by using the pop-up trimmer. Perfect for maintaining a moustache and trimming sideburns.

Pop-up trimmer



Full width, pop-up trimmer is perfect for grooming sideburns and moustache.

Battery Light

Charging indicator

Easy grip for optimal handling



This ergonomically designed grip enables easy handling for a comfortable shave.

Built to last

All of our shavers come with a 2 year worldwide guarantee and can adapt to any voltage. The long-lasting blades only need to be replaced after 2 years.

Specifications

Accessories

Maintenance: Cleaning brush, Protective cap

Service

Replacement head: Replace every 2 yrs with HQ56

Ease of use

Charging: 1 hour

Charging: Corded/cordless

Power

Automatic voltage: 100–240 V

Run time: 30 min

Shaving Performance

Shaving system: Super Lift & Cut technology

Contour-following: Reflex Action system, Individual floating heads

