

PHILIPS

8200 series

Electric shaver

With LED multi-purpose display



HQ8290/17



Fast. Close. Efficient.

The three tracks of the Speed-XL shaving heads offer 50% more shaving surface for a fast and close shave

A fast and close shave

- Speed-XL shaving heads for a fast and close shave

For a fast and efficient shave

- SmartTouch Contour-following: for a fast and efficient shave

Rinses clean in seconds

- FastRinse with anti-bacterial coating inside

Shaves even the shortest stubble

- Precision Cutting System

Comfortably close

- Super Lift & Cut technology

Highlights

Speed-XL shaving heads



The three shaving tracks offer 50% more shaving surface for a fast and close shave. *compared to standard rotary shaving heads.

SmartTouch Contour-following




Constantly keeps the 3 shaving heads in close contact with your skin for a fast and efficient shave.

FastRinse



Anti-bacterial coating inside the shaving unit ensures that the shaver is rinsed clean in seconds.

Precision Cutting System



Ultra thin heads with slots to shave the long hairs and holes to shave even the shortest stubble.

Super Lift & Cut technology



The dual blade system lifts hairs to cut comfortably below skin level.

Reflex Action system



Automatically adjusts to every curve of your face and neck.

Specifications

Shaving Performance

Shaving System: Speed XL shaving heads, Precision Cutting System, Super Lift & Cut technology

Contour-following: SmartTouch Contour-following, Reflex Action system, Individual floating heads

Styling: Precision trimmer

Categorization PC

Shavers: 8000 series

Ease of use

Display: Travel lock

Charging: Rechargeable, Corded/cordless

Charging: 1 hour

Shaving time: 17 days

Cleaning: Washable

Design

Material: Chrome

Finishing: Mirror coated display

Accessories

Stand: Charging stand

Pouch: Soft pouch

Maintenance: Cleaning brush, Protection cap

Power

Run time: 50 min

Service

Replacement head: Replace every 2 yrs with HQ9

