



3 headers

Philishave range 2002

SENSOTEC NiMH

HQ 8894 HQ 8890 HQ 8880 HQ 8870 HQ 8850 HQ 8445

Shaving system	HQ 8894	HQ 8890	HQ 8880	HQ 8870	HQ 8850	HQ 8445
Personal Comfort Control	•	•	•	•	•	•
Dual shaving heads (slots & holes)	•	•	•	•	•	•
Easy clean waterproof shaver	•	•	•	•	•	•
3D Contour following shaving system	•	•	•	•	•	•
Super Lift & cut	•	•	•	•	•	•
Individually floating heads	•	•	•	•	•	•
Silent power	•	•	•	•	•	•
Vibration free, rotating system	•	•	•	•	•	•
Long, omnidirectional slots	•	•	•	•	•	•
Hair collecting chamber	•	•	•	•	•	•

Power system

Rechargeable/mains	•	•	•	•	•	•
Mains	-	-	-	-	-	•
Charging time	1hr.	1hr.	1hr.	1hr.	1 hr.	-
Cordless shaving time up to	100'	70'	70'	70'	70'	-
NiMH 'Green Energy' cell	Li-ion*	2	2	2	2	-
Automatic voltage selection	•	•	•	•	•	-
12 Volts charging	•	•	•	•	•	-

Luxury level

Charging indication	•	•	•	•	•	-
Battery full indication	•	•	•	•	•	-
Battery low indication	•	•	•	•	•	-
Battery cap. indication	PolyLED	LCD	7 LED	5 LED	-	-
Minutes left indication	•	-	-	-	-	-
Shaving head replacem. Indicator	•	-	-	-	-	-
Cleaning advice	•	•	•	•	•	-
Soft rubber grip panel	•	•	•	•	•	•
Lacquering	•	•	•	•	•	•
Trimmer	•	•	•	•	•	•
Electronic on/off switch	•	•	•	•	•	•
Deluxe leather pouch	•	-	-	-	-	-
Deluxe pouch	-	•	•	•	•	•
Regular pouch	-	-	-	•	•	•
Stand holder	•	•	-	-	-	-

Packaging

Dimensions fancy box (mm.)	142x142x245	132x106x187	132x106x187	132x90x187	132x90x187	132x90x187
Weight fancy box (gr.)	846	566	540	533	527	564
Dimensions master carton	294x148x247	272x220x193	272x220x193	375x193x136	375x193x136	375x193x136
Weight master carton	1917	2489	2385	2357	2333	2481
Master carton contains (pcs.)	4	4	4	4	4	4

SENSOTEC NiCd

HQ 8885 HQ 8875 HQ 8865 HQ 8845 HQ 8825

Shaving system	HQ 8885	HQ 8875	HQ 8865	HQ 8845	HQ 8825
Personal Comfort Control	•	•	•	•	•
Dual shaving heads (slots & holes)	•	•	•	•	•
Easy clean waterproof shaver	•	•	•	•	•
3D Contour following shaving system	•	•	•	•	•
Super Lift & cut	•	•	•	•	•
Individually floating heads	•	•	•	•	•
Silent power	•	•	•	•	•
Vibration free, rotating system	•	•	•	•	•
Long, omnidirectional slots	•	•	•	•	•
Hair collecting chamber	•	•	•	•	•

Power system

Rechargeable/mains	•	•	•	•	•
Mains	-	-	-	-	-
Charging time	1hr.	1hr.	1hr.	1 hr.	1 hr.
Cordless shaving time up to	45'	45'	45'	45'	45'
NiCd cell	2	2	2	2	2
Automatic voltage selection	•	•	•	•	•
12 Volts charging	•	•	•	•	•

Luxury level

Charging indication	•	•	•	•	•
Battery full indication	•	•	•	•	•
Battery low indication	•	•	•	•	-
Battery cap. indication	LCD	7 LED	5 LED	-	-
Minutes left indication	•	-	-	-	-
Shaving head replacem. Indicator	-	-	-	-	-
Cleaning advice	•	•	•	•	-
Soft rubber grip panel	•	•	•	•	•
Lacquering	•	•	•	•	•
Trimmer	•	•	•	•	•
Electronic on/off switch	•	•	•	•	•
Deluxe leather pouch	-	-	-	-	-
Deluxe pouch	-	•	•	•	•
Regular pouch	-	-	•	•	•
Stand holder	•	-	-	-	-

Packaging

Dimensions fancy box (mm.)	132x106x187	132x106x187	132x90x187	132x90x187	132x90x187
Weight fancy box (gr.)	566	540	533	527	527
Dimensions master carton	272x220x193	272x220x193	375x193x136	375x193x136	375x193x136
Weight master carton	2489	2385	2357	2333	2333
Master carton contains (pcs.)	4	4	4	4	4

QUADRA ACTION NiMH

HQ 7870 HQ 7850 HQ 7415

Shaving system	HQ 7870	HQ 7850	HQ 7415
Dual shaving heads (slots & holes)	•	•	•
Easy clean waterproof shaver	•	•	•
3D Contour following shaving sys.	•	•	•
Lift & cut	•	•	•
Individually floating heads	•	•	•
Silent power	•	•	•
Vibration free, rotating system	•	•	•
Long, omnidirectional slots	•	•	•
Hair collecting chamber	•	•	•

Power system

Rechargeable/mains	•	•	-
Rechargeable	-	-	-
Mains	-	-	•
Charging time	1hr.	1hr.	-
Cordless shaving time up to	70'	70'	-
NiMH 'Green Energy' cell	2	2	-
Automatic voltage selection	•	•	-
12 Volts charging	•	•	-

Luxury level

Charging indication	•	•	-
Battery full indication	•	•	-
Battery low indication	•	•	-
Battery cap. ind.	5 LED's	-	-
Minutes left indication	-	-	-
Cleaning advice	-	-	-
Soft rubber grip panels	•	•	-
Lacquering	•	•	•
Trimmer	•	•	•
Electronic on/off switch	•	•	•
Deluxe pouch	•	•	-
Regular pouch	-	-	-
Stand/wall holder	-	-	-

Packaging

Dimensions fancy box (mm.)	133x76x187	133x76x187	133x76x187
Weight fancy box (gr.)	510	495	455
Dimensions master carton	269x224x275	269x224x275	269x224x275
Weight master carton	3300	3210	2970
Master carton contains (pcs.)	6	6	6

QUADRA ACTION NiCd

HQ 7865 HQ 7845 HQ 7825 HQ 7815 HQ 7615

Shaving system	HQ 7865	HQ 7845	HQ 7825	HQ 7815	HQ 7615
Dual shaving heads (slots & holes)	•	•	•	•	•
Easy clean waterproof shaver	•	•	•	•	•
3D Contour following shaving sys.	•	•	•	•	•
Lift & cut	•	•	•	•	•
Individually floating heads	•	•	•	•	•
Silent power	•	•	•	•	•
Vibration free, rotating system	•	•	•	•	•
Long, omnidirectional slots	•	•	•	•	•
Hair collecting chamber	•	•	•	•	•

Power system

Rechargeable/mains	•	•	•	•	-
Rechargeable	-	-	-	-	•
Mains	-	-	-	-	-
Charging time	1hr.	1hr.	1hr.	8 hr.	8 hr.
Cordless shaving time up to	45'	45'	45'	45'	45'
NiCd cell	2	2	2	2	2
Automatic voltage selection	•	•	•	•	-
12 Volts charging	•	•	•	-	-

Luxury level

Charging indication	•	•	•	•	•
Battery full indication	•	•	•	-	-
Battery low indication	•	•	-	-	-
Battery cap. ind.	5 LED's	-	-	-	-
Minutes left indication	-	-	-	-	-
Cleaning advice	-	-	-	-	-
Soft rubber grip panels	•	•	-	-	-
Hard grip panels	-	-	•	-	-
Lacquering	•	•	-	-	-
Trimmer	•	•	•	•	•
Electronic on/off switch	•	•	•	•	•
Deluxe pouch	•	•	-	-	-
Regular pouch	-	-	•	•	•
Stand/wall holder	-	-	-	-	-

Packaging

Dimensions fancy box (mm.)	133x76x187	133x76x187	133x76x187	133x76x187	133x76x187
Weight fancy box (gr.)	510	495	495	495	495
Dimensions master carton	269x224x275	269x224x275	269x224x275	269x224x275	269x224x275
Weight master carton	3300	3210	3210	3210	3210
Master carton contains (pcs.)	6	6	6	6	6

REFLEX ACTION NiMH

HQ 5866 HQ 5846 HQ 5826

Shaving system	HQ 5866	HQ 5846	HQ 5826
Dual shaving heads (slots & holes)	-	-	-
Easy clean waterproof shaver	-	-	-
3D Contour following shaving sys.	•	•	•
Lift & cut	•	•	•
Individually floating heads	•	•	•
Silent power	•	•	•
Vibration free, rotating system	•	•	•
Long, omnidirectional slots	•	•	•
Hair collecting chamber	•	•	•

Power system

Rechargeable/mains	•	•	•
Rechargeable	-	-	-
Mains	-	-	-
Charging time	1hr.	1hr.	1h
Cordless shaving time up to	70'	70'	70'
NiMH 'Green Energy' cell	2	2	2
Automatic voltage selection	•	•	•
12 Volts charging	-	-	-

Luxury level

Charging indication	•	•	•
Battery full indication	•	•	•
Battery low indication	•	•	•
5 Segment charge cap. ind.	LCD	LED's	-
Minutes left indication	-	-	-
Cleaning advice	-	-	-
Soft rubber grip panels	•	•	-
Metallic lacquer	•	•	-
Dual metallic lacquer	-	-	-
Trimmer	•	•	•
Electronic on/off switch	•	-	-
Deluxe storage cassette	•	-	-
Deluxe pouch	-	•	•
Regular pouch	-	-	-
Stand/wall holder	-	-	-

Packaging

Dimensions fancy box (mm.)	134x71x189	134x71x189	134x71x189
Weight fancy box (gr.)	463	401	397
Dimensions master carton	222x199x282	222x199x282	222x199x282
Weight master carton	3000	2630	2600
Master carton contains (pcs.)	6	6	6

* Instead of NiMH this is a li-ion battery



REFLEX ACTION NiMH (continued)

	HQ 5816	HQ 5806	HQ 5800	HQ 5461	HQ 5421	HQ 5401
Shaving system						
Dual shaving heads (slots & holes)	-	-	-	-	-	-
Easy clean waterproof shaver	-	-	-	-	-	-
3D Contour following shaving syst.	●	●	●	●	●	●
Lift & cut	●	●	●	●	●	●
Individually floating heads	●	●	●	●	●	●
Silent power	●	●	●	●	●	●
Vibration free, rotating system	●	●	●	●	●	●
Long, omnidirectional slots	●	●	●	●	●	●
Hair collecting chamber	●	●	●	●	●	●
Power system						
Rechargeable/mains	●	●	●	-	-	-
Rechargeable	-	-	-	-	-	-
Mains	-	-	-	●	●	●
Charging time	1 hr.	1 hr.	16 hr.	-	-	-
Cordless shaving time up to	30'	30'	30'	-	-	-
NiMH 'Green Energy' cell	1	1	1	-	-	-
Automatic voltage selection	●	●	●	●	●	●
12 Volts charging	-	-	-	-	-	-
Luxury level						
Charging indication	●	●	●	-	-	-
Battery full indication	●	●	●	-	-	-
Battery low indication	-	-	-	-	-	-
5 Segment charge cap. ind.	-	-	-	-	-	-
Minutes left indication	-	-	-	-	-	-
Cleaning advice	-	-	-	-	-	-
Soft rubber grip panels	-	-	-	-	-	-
Metallic lacquer	-	-	-	-	-	-
Dual metallic lacquer	-	-	-	-	-	-
Trimmer	●	●	●	●	●	●
Electronic on/off switch	-	-	-	-	-	-
Deluxe storage cassette	-	-	-	●	-	-
Deluxe pouch	-	-	-	-	●	-
Regular pouch	●	●	●	-	-	●
Stand/wall holder	-	-	-	-	-	-
Packaging						
Dimensions fancy box (mm.)	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189
Weight fancy box (gr.)	364	371	369	398	337	338
Dimensions master carton	222x199x282	222x199x282	222x199x282	222x199x282	222x199x282	222x199x282
Weight master carton	2400	2450	2430	2610	2240	2290
Master carton contains (pcs.)	6	6	6	6	6	6

REFLEX ACTION NiCd

	HQ 5861	HQ 5841	HQ 5821	HQ 5811	HQ 5801	HQ 5601
Shaving system						
Dual shaving heads (slots & holes)	-	-	-	-	-	-
Easy clean waterproof shaver	-	-	-	-	-	-
3D Contour following shaving syst.	●	●	●	●	●	●
Lift & cut	●	●	●	●	●	●
Individually floating heads	●	●	●	●	●	●
Silent power	●	●	●	●	●	●
Vibration free, rotating system	●	●	●	●	●	●
Long, omnidirectional slots	●	●	●	●	●	●
Hair collecting chamber	●	●	●	●	●	●
Power system						
Rechargeable/mains	●	●	●	●	●	-
Rechargeable	-	-	-	-	-	●
Mains	-	-	-	-	-	-
Charging time	1/2hr.	1hr.	1hr.	1 hr.	8 hr.	8 hr.
Cordless shaving time up to	45'	45'	45'	30'	45'	45'
NiCad cells	2	2	2	1	2	2
Automatic voltage selection	●	●	●	●	●	●
12 Volts charging	-	-	-	-	-	-
Luxury level						
Charging indication	●	●	●	●	●	●
Battery full indication	●	●	●	●	-	-
Battery low indication	●	●	●	-	-	-
5 Segment charge cap. ind.	LCD	LED's	-	-	-	-
Minutes left indication	-	-	-	-	-	-
Cleaning advice	-	-	-	-	-	-
Soft rubber grip panels	●	●	-	-	-	-
Metallic lacquer	●	●	-	-	-	-
Dual metallic lacquer	-	-	-	-	-	-
Trimmer	●	●	●	●	●	●
Electronic on/off switch	●	-	-	-	-	-
Deluxe storage cassette	●	-	-	-	-	-
Deluxe pouch	-	●	●	-	-	-
Regular pouch	-	-	-	●	●	●
Stand/wall holder	-	-	-	-	-	-
Packaging						
Dimensions fancy box (mm.)	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189
Weight fancy box (gr.)	455	388	390	364	383	378
Dimensions master carton	222x199x282	222x199x282	222x199x282	222x199x282	222x199x282	222x199x282
Weight master carton	2950	2550	2560	2400	2520	2490
Master carton contains (pcs.)	6	6	6	6	6	6

MICRO ACTION NiMH

	HQ 4866	HQ 4856	HQ 4846	HQ 4826	HQ 4807	HQ 4806	HQ 4441	HQ 4421	HQ 4411	HQ 4407	HQ 4401
Shaving system											
Dual shaving heads (slots & holes)	-	-	-	-	-	-	-	-	-	-	-
Easy clean waterproof shaver	-	-	-	-	-	-	-	-	-	-	-
3D Contour following shaving syst.	-	-	-	-	-	-	-	-	-	-	-
Lift & cut	●	●	●	●	●	●	●	●	●	●	●
Individually floating heads	●	●	●	●	●	●	●	●	●	●	●
Micro groove	●	●	●	●	●	●	●	●	●	●	●
Silent power	-	-	-	-	-	-	-	-	-	-	-
Vibration free, rotating system	●	●	●	●	●	●	●	●	●	●	●
Long, omnidirectional slots	●	●	●	●	●	●	●	●	●	●	●
Hair collecting chamber	●	●	●	●	●	●	●	●	●	●	●
Power system											
Rechargeable/mains	●	●	●	●	●	●	-	-	-	-	-
Rechargeable	-	-	-	-	-	-	-	-	-	-	-
Mains	-	-	-	-	-	-	●	●	●	●	●
Charging time	1hr.	1hr.	1hr.	8hr.	16hr.	16hr.	-	-	-	-	-
Cordless shaving time	70'	30'	30'	30'	30'	30'	-	-	-	-	-
NiMH 'Green Energy' cell	2	2	1	1	1	1	-	-	-	-	-
Automatic voltage selection	●	●	●	●	●	●	●	●	●	●	●
Manual voltage selection	-	-	-	-	-	-	-	-	-	-	-
12 Volts charging	-	-	-	-	-	-	-	-	-	-	-
Luxury level											
Charging indication	●	●	●	●	●	●	-	-	-	-	-
Battery full indication	●	●	●	●	●	●	-	-	-	-	-
Battery low indication	●	●	●	-	-	-	-	-	-	-	-
5 Segment charge cap. ind.	LED's	-	-	-	-	-	-	-	-	-	-
Minutes left indication	-	-	-	-	-	-	-	-	-	-	-
Cleaning advice	-	-	-	-	-	-	-	-	-	-	-
Soft grip panels	-	-	-	-	-	-	-	-	-	-	-
Metallic lacquer	●	●	-	-	-	-	●	●	●	●	●
Dual metallic lacquer	-	-	-	-	-	-	-	-	-	-	-
Translucent	-	-	-	-	●	-	-	-	-	●	-
Trimmer	●	●	●	●	●	●	●	●	●	●	●
Electronic on/off switch	-	-	-	-	-	-	-	-	-	-	-
Deluxe storage cassette	-	-	-	-	-	-	-	-	-	-	-
Deluxe pouch	●	-	-	-	-	-	●	●	●	●	●
Regular pouch	-	●	●	●	●	●	-	-	-	-	-
Stand/wall holder	-	-	-	-	-	-	-	-	-	-	-
Packaging											
Dimensions fancy box (mm.)	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189
Weight fancy box (gr.)	465	443	435	413	435	410	410	410	410	400	400
Dimensions master carton	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282
Weight master carton	3010	2880	2830	2720	2830	2830	2680	2680	2680	2620	2620
Master carton contains (pcs.)	6	6	6	6	6	6	6	6	6	6	6

MICRO ACTION NiCd

	HQ 4861	HQ 4851	HQ 4821	HQ 4607	HQ 4606
Shaving system					
Dual shaving heads (slots & holes)	-	-	-	-	-
Easy clean waterproof shaver	-	-	-	-	-
3D Contour following shaving syst.	-	-	-	-	-
Lift & cut	●	●	●	●	●
Individually floating heads	●	●	●	●	●
Micro groove	●	●	●	●	●
Silent power	-	-	-	-	-
Vibration free, rotating system	●	●	●	●	●
Long, omnidirectional slots	●	●	●	●	●
Hair collecting chamber	●	●	●	●	●
Power system					
Rechargeable/mains	●	●	●	-	-
Rechargeable	-	-	-	●	●
Mains	-	-	-	-	-
Charging time	1hr.	1hr.	8hr.	16hr.	16hr.
Cordless shaving time	45'	45'	45'	30'	30'
NiCad cells	2	2	2	1	1
Automatic voltage selection	●	●	●	-	-
Manual voltage selection	-	-	-	●	●
12 Volts charging	-	-	-	-	-
Luxury level					
Charging indication	●	●	●	●	●
Battery full indication	●	●	●	-	-
Battery low indication	●	●	-	-	-
5 Segment charge cap. ind.	LED's	-	-	-	-
Minutes left indication	-	-	-	-	-
Cleaning advice	-	-	-	-	-
Soft grip panels	-	-	-	-	-
Metallic lacquer	●	●	-	-	-
Dual metallic lacquer	-	-	-	-	-
Translucent	-	-	-	●	-
Trimmer	●	●	●	●	●
Electronic on/off switch	-	-	-	-	-
Deluxe storage cassette	-	-	-	-	-
Deluxe pouch	●	-	-	-	-
Regular pouch	-	●	●	●	●
Stand/wall holder	-	-	-	-	-
Packaging					
Dimensions fancy box (mm.)	134x71x189	134x71x189	134x71x189	134x71x189	134x71x189
Weight fancy box (gr.)	465	465	465	467	467
Dimensions master carton	224x199x282	224x199x282	224x199x282	224x199x282	224x199x282
Weight master carton	3010	3010	3010	3020	3020
Master carton contains (pcs.)	6	6	6	6	6