

Beard Trimmers
Hair Clippers



International range

(note: not all models will be available in all countries)



BEARD TRIMMERS

	T788	T784	T764	T562	T502
Trimming system					
Contour Tracking System™, comb adapts to the contours of the face	●	●	●	●	●
Precision Zoom Lock™, ring on appliance	●	●	●	-	-
Adjustment integrated in comb	-	-	-	●	●
Stubble setting	●	●	●	●	●
Range of beard lengths (mm)	0.7-18	0.7-18	0.7-18	0.7-7	0.7-7
Number of length settings	9	9	9	4	4
Cutter width (mm)	32	32	32	32	32
Pop-up precision trimmer	●	-	-	-	-
Extremely sharp teeth for best cutting performance	●	●	●	●	●
3-dimensional rounded teeth for skin comfort	●	●	●	●	●
Maintenance free cutting element	●	●	●	●	●
Hinge cutting element for brush cleaning	●	●	●	●	●
Power system					
Rechargeable and mains	●	●	-	-	-
Rechargeable	-	-	●	●	-
Battery	-	-	-	-	●
Charging time in hours (NiMH/NiCd)	1/1	14/10	14/10	14/10	-
Cordless operation time in minutes (NiMH/NiCd)	50/40	50/40	50/40	50/40	130 (alkaline)
Automatic voltage selection	●	●	-	-	-
Charging indication	●	●	●	●	-
Battery Full Indication	●	-	-	-	-
Luxury level					
Soft touch grip	●	●	●	-	-
Metallic finishing	●	●	-	-	-
Cleaning brush	●	●	●	●	●
Pouch	●	-	-	-	-
Packaging					
Dimensions fancy box (mm)	105 x 105 x 224	105 x 105 x 224	105 x 105 x 224	105 x 105 x 224	90 x 71 x 224
Weight fancy box (gr.)	426	373	421	420	246
Dimensions master carton (mm)	325 x 234 x 234	325 x 234 x 234	325 x 234 x 234	325 x 234 x 234	280 x 166 x 234
Weight master carton (gr.)	2825	2510	2794	2800	1661
Master carton contains (pcs)	6	6	6	6	6



International range

(note: not all models will be available in all countries)



HAIR CLIPPERS

	C688	C644	C484	C442	C281	C241
Clipping system						
Contour Tracking System™, comb adapts to contours of head	●	●	-	-	-	-
Additional Large comb for longer hair styling results	●	●	●	●	-	-
Translucent comb material for good view on cutting process	●	●	-	-	-	-
Precision Zoom Lock™, ring on appliance	●	●	-	-	-	-
Shift lock on appliance with locking button	-	-	●	●	-	-
Adjustment on back of the comb	-	-	-	-	●	●
Range of hair lengths (mm)	4-40	4-40	4-40	4-40	4-21	4-21
Number of length settings	2 x 7	2 x 7	2 x 7	2 x 7	7	7
Cutter width (mm)	41	41	32	32	32	32
Extremely sharp teeth for best cutting performance	●	●	●	●	●	●
3-dimensional rounded teeth for skin comfort	●	●	●	●	●	●
Maintenance free cutting element	●	●	●	●	●	●
Hinge/Detachable cutting unit for brush cleaning	H	H	D	D	D	D
Power system						
Rechargeable and mains (pilot light to indicate charging)	●	-	●	-	●	-
Mains	-	●	-	●	-	●
Charging time in hours (NiCd/NiMH)	12/12	-	10/12	-	10/12	-
Cordless operation time in minutes (NiCd/NiMH)	50/50	-	40/50	-	40/50	-
Accessories						
Instruction video	●	●	-	-	-	-
Instruction booklet	●	●	●	●	-	-
Cassette/Pouch	C	P	P	-	-	-
Cape	●	-	-	-	-	-
Scissors	●	●	●	●	●	●
Styling comb and cleaning brush	●	●	●	●	●	●
Metallic product finishing	●	●	-	-	-	-
Soft touch operation elements	●	●	-	-	-	-
Packaging						
Dimensions fancy box (mm)	250 x 97 x 240	250 x 97 x 240	195x81 x 240	195 x 67 x 240	140 x 64 x 230	140 x 64 x 230
Weight fancy box (gr.)	1400	1100	860	740	630	570
Dimensions master carton (mm)	509 x 324 x 250	509 x 324 x 250	501 x 205 x 272	417 x 205 x 272	430 x 240 x 155	430 x 240 x 155
Weight master carton (gr.)	8800	7000	5600	4800	3790	3730
Master carton contains (pcs)	6	6	6	6	6	6