

PHILIPS

Hand blender

Viva Collection

650 W, metal bar

Double action knife

1 L Beaker, chopper

16 speeds +turbo



HR1614/00



Enjoy homemade food and drinks any day Hand blender with various speeds

The Philips hand blender combines 650 Watt power with a double-action blade and multiple speed settings, giving a wonderfully smooth result in seconds. Preparing healthy and delicious homemade food has never been so easy!

A smooth result in seconds

- Double action blade
- Select the optimal speed for all type of ingredients
- Extra powerful turbo button for the toughest ingredients
- Powerful 650 W motor

Easy processing and storing

- Soft touch grip and buttons
- 1L measuring handblender beaker

No splashing while you blend

- Anti-splash blade guard with special wave shape

Quick and easy cleaning

- Detachable stainless steel shaft

Highlights

16-speeds and turbo



With 16 speed settings you can select the optimal speed for all type of ingredients creating the preferred consistency or smoothest blending results.

Turbo button

For the toughest ingredients.

Double-action blade



Double action blade of the Philips hand blender cuts horizontally and vertically.

Soft touch grip and buttons

The soft touch grip and buttons provide comfort when using the product.

Detachable stainless steel shaft

Detachable stainless steel shaft

1 L beaker



With the 1L beaker you can measure the ingredients for your recipes, but also quickly blend soups, purees or shakes .

Anti-splash blade guard



The special wave shape in the bottom part of the handblender blending bar guarantees no splashes or mess while you blend.

Powerful 650 W motor

650 W

Powerful 650 W motor

Specifications

Design specifications

Color(s): White and lavender

Material bar: Metal

Material blade: Stainless steel

Material housing: PP and rubber

Material jar: SAN

General specifications

Turbo function

Detachable shaft: With 2 buttons

Speed setting: 16

Accessories

Beaker

Technical specifications

Capacity beaker: 1 L

Frequency: 50/60 Hz

Voltage: 220-240 V

Wattage: 650 W

Cord length: 1.3 m

