

Hand blender

Viva Collection

650 W, metal bar

Double action knife

1 L Beaker, chopper

16 speeds +turbo



HR1615/90



## Enjoy homemade food and drinks any day Easy blending and chopping at various speeds

The Philips hand blender combines 650 Watt power with a double-action blade and multiple speed settings, giving a wonderfully smooth result in seconds. Preparing healthy and delicious homemade food has never been so easy!

### A smooth result in seconds

- Double action blade
- Select the optimal speed for all type of ingredients
- Extra powerful turbo button for the toughest ingredients
- Powerful 650 W motor

### Easy processing and storing

- Soft touch grip and buttons
- Chopper accessory
- 1L measuring handblender beaker

### No splashing while you blend

- Anti-splash blade guard

### Quick and easy cleaning

- Detachable stainless steel shaft

# Highlights

**16-speeds and turbo**

With 16 speed settings you can select the optimal speed for all type of ingredients creating the preferred consistency or smoothest blending results.

**Turbo button**

For the toughest ingredients.

**Double-action blade**

Double action blade of the Philips hand blender cuts horizontally and vertically.

**Anti-splash blade guard**

No splashes or mess while you blend.

**Chopper accessory**

Chopper accessory to chop onion, cheese and more.

**Soft touch grip and buttons**

The soft touch grip and buttons provide comfort when using the product.

**Detachable stainless steel shaft**

Detachable stainless steel shaft

**1 L beaker**

With the 1L beaker you can measure the ingredients for your recipes, but also quickly blend soups, purees or shakes .

**Powerful 650 W motor**

# 650W

Powerful 650 W motor

# Specifications

**Design specifications**

**Color(s):** Black and silver  
**Material bar:** Metal  
**Material housing:** PP and rubber  
**Material blade:** Stainless steel  
**Material jar:** SAN

**General specifications**

**Turbo function**  
**Detachable shaft:** With 2 buttons  
**Speed setting:** 16

**Accessories**

**Chopper:** Compact chopper  
**Beaker:** 1 L

**Technical specifications**

**Frequency:** 50/60 Hz  
**Voltage:** 220–240 V  
**Wattage:** 650 W  
**Cord length:** 1.3 m  
**Capacity beaker:** 1 L

