

# PHILIPS

Hand blender

Viva Collection

650 W

Metal bar, double action knife

2 accessories

16 speeds +turbo



HR1616/00



## Enjoy homemade food and drinks any day

### Easy blending, mashing and whisking at any speed

The Philips hand blender combines 650 Watt power with a double-action blade and multiple speed settings, giving a wonderfully smooth result in seconds. Preparing healthy and delicious homemade food has never been so easy!

#### Easy processing and storing

- Masher accessory for smoothest mashed potatoes
- Whisk accessory for whipping cream and mayonnaise
- Soft touch grip and buttons
- 1L measuring handblender beaker

#### A smooth result in seconds

- Double action blade
- Select the optimal speed for all type of ingredients
- Extra powerful turbo button for the toughest ingredients
- Powerful 650 W motor

#### No splashing while you blend

- Anti-splash blade guard with special wave shape

# Highlights

## 16-speeds and turbo



With 16 speed settings you can select the optimal speed for all type of ingredients creating the preferred consistency or smoothest blending results.

## Double-action blade



Double action blade of the Philips hand blender cuts horizontally and vertically.

## Masher accessory



With the masher accessory for the Philips hand blender you can mash potatoes silky smooth.

## Soft touch grip and buttons

The soft touch grip and buttons provide comfort when using the product.

## Turbo button

For the toughest ingredients.

## Whisk accessory for whipping



Whisk accessory for whipping cream and mayonnaise

## Anti-splash blade guard



The special wave shape in the bottom part of the handblender blending bar guarantees no splashes or mess while you blend.

## Powerful 650 W motor

# 650 W

Powerful 650 W motor

## 1 L beaker



With the 1L beaker you can measure the ingredients for your recipes, but also quickly blend soups, purees or shakes .

# Specifications

## Accessories

Potato masher  
Whisk  
Beaker: 1 L

## Design specifications

Color(s): White and lavender  
Material bar: Metal  
Material blade: Stainless steel  
Material housing: PP and rubber  
Material jar: SAN

## General specifications

Turbo function  
Speed setting: 16

## Technical specifications

Capacity beaker: 1.0 l  
Wattage: 650 W  
Voltage: 220–240 V  
Frequency: 50/60 Hz  
Cord length: 1.3 m

