

PHILIPS

Hand blender

Viva Collection

650 W, metal bar

Double action knife

1,7 L Beaker, XL chopper, whisk

16 speeds +turbo



HR1617/01



Enjoy homemade food and drinks any day Easy blending, chopping, and whisking at any speed

The Philips hand blender combines 650 Watt power with a double-action blade and multiple speed settings, giving a wonderfully smooth result in seconds. Preparing healthy and delicious homemade food has never been so easy!

A smooth result in seconds

- Double action blade
- Select the optimal speed for all type of ingredients
- Extra powerful turbo button for the toughest ingredients
- Powerful 650 W motor

Easy processing and storing

- 1.7L oval beaker for preparing food or storing the appliance
- Soft touch grip and buttons
- Whisk accessory for whipping cream and mayonnaise
- XL chopper accessory for chopping large quantities

No splashing while you blend

- Anti-splash blade guard

Quick and easy cleaning

- Detachable stainless steel shaft

Highlights

16-speeds and turbo



With 16 speed settings you can select the optimal speed for all type of ingredients creating the preferred consistency or smoothest blending results.

Turbo button

For the toughest ingredients.

Double-action blade



Double action blade of the Philips hand blender cuts horizontally and vertically.

Anti-splash blade guard



No splashes or mess while you blend.

1.7 L oval beaker



1.7L oval beaker for preparing food or storing the appliance

XL chopper



XL chopper accessory for chopping large quantities of nuts, onions, meat, and more.

Whisk accessory for whipping



Whisk accessory for whipping cream and mayonnaise

Detachable stainless steel shaft

Detachable stainless steel shaft

Soft touch grip and buttons

The soft touch grip and buttons provide comfort when using the product.

Powerful 650 W motor

650 W

Powerful 650 W motor

Specifications

Design specifications

Color(s): White and lavender
Material bar: Metal
Material blade: Stainless steel
Material housing: PP and rubber
Material jar: SAN

General specifications

Turbo function
Detachable shaft: With 2 buttons
Speed setting: 16

Accessories

Chopper: XL chopper
Whisk

Technical specifications

Capacity beaker: 1.7 l
Frequency: 50/60 Hz
Voltage: 220–240 V
Wattage: 650 W
Cord length: 1.3 m

