

PHILIPS

Hand blender

Viva Collection

650 W, metal bar

Double-action knife

1.7 L Beaker, XL chopper, whisk

16 speeds + turbo



HR1617/81



Enjoy homemade food and drinks any day Easy blending, chopping and whisking at any speed

The Philips hand blender combines 650 Watts of power with a double-action blade and multiple speed settings, giving a wonderfully smooth result in seconds. Preparing healthy and delicious homemade food has never been so easy!

A smooth result in seconds

- Select the optimal speed for all types of ingredients
- Double action blade
- Powerful 650-W motor
- Extra powerful turbo button for the toughest ingredients

Easy processing and storing

- Soft touch grip and buttons
- Whisk accessory for whipping cream and mayonnaise
- XL chopper accessory for chopping large quantities
- 1.7 l oval beaker for preparing food or storing the appliance

No splashing while you blend

- Anti-splash blade guard with special wave shape

Quick and easy cleaning

- Detachable stainless steel shaft

Highlights

Double action blade



The double-action blade of the Philips hand blender cuts horizontally and vertically.

Whisk accessory for whipping



Whisk accessory for whipping cream and mayonnaise

Turbo button



For the toughest ingredients.

Soft touch grip and buttons



The soft touch grip and buttons provide comfort when using the product.

1.7 l oval beaker



1.7 l oval beaker for preparing food or storing the appliance

Anti-splash blade guard



The special wave shape in the bottom part of the hand blender blending bar guarantees no splashes or mess while you blend.

Detachable stainless steel shaft



Detachable stainless steel shaft

16 speeds and turbo



With 16 speed settings you can select the optimal speed for all types of ingredients, creating the preferred consistency or the smoothest blending results.

Powerful 650-W motor

650W

Powerful 650-W motor

XL chopper



XL chopper accessory for chopping large quantities of nuts, onions, meat and more.

Specifications

Accessories

Chopper: XL chopper
Whisk

Design specifications

Material bar: Metal
Material housing: PP and rubber
Material blade: Stainless steel
Material jar: SAN

General specifications

Speed setting: 16
Turbo function

Technical specifications

Cord length: 1.3 m
Frequency: 50/60 Hz
Voltage: 220-240 V
Wattage: 650 W
Capacity beaker: 1.7 l

