

PHILIPS

Hand blender

Avance Collection

600 W

metal bar

3 accessories



HR1652/90



Maximum results, minimum effort

Revolutionary thumb-grip design for easy handling

The Avance Collection hand blender has a revolutionary thumb-grip design and combines a strong and durable motor with multiple speed settings (20), giving you the power, speed, and confidence to create maximum results with minimum effort.



Comfortable grip and easy handling

- Single-button release
- Thumb-grip design

A smooth result in seconds

- Extra powerful turbo button
- 20 speed settings

Easy processing and storing

- Protection cap to protect blending knife when stored
- 1L beaker with lid to store soups, puree or shake

Chops onion, herbs, hard cheese and more

- XL chopper accessory for chopping large quantities
- Serrated blades for ice crushing in XL chopper

No splashing while you blend

- Anti-splash blade guard



asimpleswitch.com

Highlights

Thumb-grip design



Thumb-grip design with large switches.

Single-button release



Single-button release for easy assembly and disassembly.

20 speed settings



20 speed settings for optimal performance.

Extra powerful turbo button



The Philips hand blender has an extra powerful turbo button for the toughest ingredients.

1L beaker with lid



1L beaker with lid to store soups, puree or shake

XL chopper accessory



With the XL chopper accessory (1000ml) for a Philips hand blender you can chop large quantities of meat, herbs, nuts, cheese, chocolate and onions in seconds.

Serrated blades for XL chopper accessory



Serrated blades for ice crushing in XL chopper

Protection cap



Protection cap to protect blending knife when stored

Anti-splash blade guard



No splashes or mess while you blend.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Design specifications

Available color(s): Ink black

Material blade: Stainless steel

Material housing: Stainless steel and PP

Material jars: SAN

Material shaft: Stainless steel

General specifications

Detachable shaft

Speeds: 20 speeds

Turbo function

Accessories

Chopper: XL chopper

Protection cap

Serrated blades for XL chopper

Beaker with lid: 1 L

Technical specifications

Power: 600 W

Voltage: 220-240 V

