

PHILIPS

Hand blender

600 W

Metal bar

with cube cutter



HR1659/98



Maximum results, minimum effort

Prepare a perfect homemade Olivier salad in seconds

The Avance Collection hand blender with cube cutter accessory allows you to make perfect cubes in seconds. The strong motor and revolutionary thumb-grip design will give you the power and speed to create maximum results with minimum effort.

A smooth result in seconds

- Powerful 600 Watt motor
- Extra powerful turbo button
- 20 speed settings

Easy processing and storing

- Protection cap to protect blending knife when stored
- 1L beaker with lid to store soups, puree or shake
- Thumb-grip design
- Specially designed cleaning tool for easy cleaning

Prepare ingredients any way you like

- Chopper to chop herbs, nuts, cheese, chocolate and onions
- Kneading hook for making dough
- Double sided slicing and grating disk
- Unique cube cutting accessory



asimpleswitch.com

Highlights

Powerful 600 Watt motor

600W

To blend food in seconds.

Extra powerful turbo button



The Philips hand blender has an extra powerful turbo button for the toughest ingredients.

Protection cap



Protection cap to protect blending knife when stored

20 speed settings



20 speed settings for optimal performance.

1L beaker with lid



1L beaker with lid to store soups, puree or shake

Kneading hook for making dough



Kneading hook for making dough

Compact chopper accessory



With the compact chopper accessory of the Philips hand blender you can chop herbs, nuts, cheese, chocolate and onions.

Slicing and grating disk



With the double sided slicing and grating disk you can process vegetables quickly. Simply flip the disk to slice or grate all kind of vegetables.

Unique cube cutting accessory



Unique cube cutting accessory



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Design specifications

Material housing: Stainless steel and PP

Material jars: SAN

Material blade: Stainless steel

Material shaft: Stainless steel

Color(s): Ink black

General specifications

Speeds: 20 speeds

Turbo function

Detachable shaft

Accessories

Cube cutter

Food Processor Accessory

Slicing and grating disk

Kneading hook

Chopper: Compact chopper

Beaker

Protection cap

Technical specifications

Capacity food processor: 1.5 L

Capacity beaker: 1 L

Voltage: 220-240 V

Power: 600 W

