

# PHILIPS

## Juicer

Avance Collection

900 W

QuickClean

2.5 l, XXL tube

Drip stop

HR1869/71



## Maximum juice. Minimum fuss.

Make 10% more juice\* and rinse clean!

The Philips Avance Collection juicer squeezes every drop from your fruits and vegetables, thanks to the upside-down sieve concept. With QuickClean technology, cleaning your juicer has never been easier.

### **Squeeze every drop from your fruit and vegetables**

- Extract 10% more juice
- Make up to 2.5 litres of juice in one go
- Juice the toughest ingredients - 900 W
- No pre-cutting needed thanks to XXL feeding tube
- 2 speeds for soft or hard fruit and vegetables

### **Quick and easy cleaning**

- QuickClean technology with polished sieve
- Pre-clean function rinses away the unwanted fibres
- Easily wipe away the fibres from the smooth sieve surface
- All pulp collected in one place for easy disposal
- All parts are dishwasher safe

### **Easy to use**

- Quick and easy assembly of all parts
- Drip stop to prevent juice from dripping

# Highlights

## 10% more juice



Thanks to the innovative juice extraction system with upside-down sieve, the juicer squeezes every drop out of your fruits and vegetables, creating a juice fountain. You get up to 10% more juice compared to Philips' number one juicer HR1861.

## Make 2.5 L in one go



Thanks to the innovative juice extraction system with the upside down sieve, this juicer extracts up to 10% more juice\*. And depending on the type of fruit or vegetables you juice, it is possible to make up to 2.5 litres of juice in one go without the need to empty the pulp container.

## 900 W

Juice the toughest ingredients with a powerful 900-W motor.

## XXL feeding tube



The 80 mm extra large feeding tube allows you to juice even large fruit and vegetables like apples, carrots and beetroots without pre-cutting.

## 2 speeds



2 speeds for soft or hard fruit and vegetables

## QuickClean technology



The Philips juicer is designed for easy cleaning thanks to QuickClean technology. Cleaning is now as simple as rinsing, thanks to the pre-clean function and the QuickClean polished sieve.

## Pre-clean function



The Philips juicer is the 1st centrifugal juicer on the market with a pre-clean function. By pouring water into the pusher, you can create a water fountain in the appliance, which rinses away the unwanted fibres from the lid and makes the sieve easier to clean.

## QuickClean polished sieve



A lot of pulp fibres get stuck in a standard sieve, which makes it very difficult to clean. That is not the case for the QuickClean polished sieve of the Philips Juicer, as all surfaces of the sieve are smooth. After pre-cleaning, you can easily wipe away the remaining fibres with a standard kitchen brush. The entire juicer can now be cleaned within a minute!

## Integrated pulp container



The pulp will all be collected in the only place where it should be: in the pulp container of your Philips juicer. That means you no longer need to remove pulp from other parts such as the lid. Due to the round design and smooth surfaces without nooks and crannies, the pulp is easy to reach and the container is much easier to clean.

## Dishwasher safe



All removable parts can be cleaned in the dishwasher.

# Specifications

## Design specifications

Colour(s): Black

## General specifications

2 speeds

Drip-stop

## Technical specifications

Power: 900 W

Capacity: 2.5 l

## Accessories

Spout accessory

## Easy to clean

Dishwasher-safe accessories

QuickClean

