

PHILIPS

Juicer

Avance Collection

1000 W

QuickClean

2.5 L, XXL tube

Drip stop, citrus press

HR1874/70



Maximum juice. Minimum fuss.

Make 10% more juice* and rinse clean!

Philips Avance Collection juicer squeezes every drop from your fruits and vegetables, thanks to the upside-down sieve. Now with a citrus juicer for more variety. With QuickClean technology cleaning your juicer has never been easier.

Squeeze every drop from your fruits and vegetables

- Extract 10% more juice
- Make up to 2.5 liters of juice in one go
- No pre-cutting needed thanks to XXL feeding tube
- 2 speeds for soft or hard fruit and vegetables
- Citrus juicer accessory
- Juice the toughest ingredients - 1000 W

Quick and easy cleaning

- QuickClean technology with polished sieve
- Pre-clean function rinses away the unwanted fibers
- Easily swipe away the fibers from the smooth surface sieve
- All pulp collected in one place for easy disposal
- All parts are dishwasher safe

Easy to use

- Quick and easy assembly of all parts

Highlights

10% more juice



Thanks to the innovative juice extraction system with upside down sieve, the juicer squeezes every drop of your fruits and vegetables, creating a juice fountain. You get up to 10% more juice, compared to Philips' number one juicer HR1861.

Make 2.5 L in one go



Thanks to the innovative juice extraction system with the upside down sieve, this juicer extracts up to 10% more juice*. And depending on the type of fruit or vegetables one juices, it is possible to make up to 2.5 liters of juice in one go without the need to empty the pulp container.

XXL feeding tube



The 80 mm extra large feeding tube allows you to juice even large fruits and vegetables like apples, carrots and beetroots without pre-cutting.

2 speeds



2 speeds for soft or hard fruit and vegetables

Citrus juicer accessory



Thanks to the Citrus juicer accessory you can make fresh home made orange juice every day. The self-rotating system uses an optimal speed to help you juice fast and easy. No more pressing force is needed.

QuickClean technology



The Philips juicer is designed for easy cleaning thanks to QuickClean technology. Cleaning is now as simple as rinsing, thanks to the pre-clean function and the QuickClean polished sieve.

Pre-clean function



The Philips juicer is the 1st centrifugal juicer on the market with a pre-clean function. By pouring water in the pusher, you can create a water fountain in the appliance, which rinses away the unwanted fibers from the lid and makes the sieve easier to clean.

QuickClean polished sieve



A lot of pulp fibers get stuck in a standard sieve which makes it very difficult to clean. That is not the case for the QuickClean polished sieve of the Philips Juicer, as all surfaces of the sieve are smooth. After pre-cleaning, you can easily swipe away the remaining fibers with a standard kitchen brush. The complete juicer can now be cleaned within a minute!

Integrated pulp container



The pulp will all be collected in the only place where it should be: in the pulp container of your Philips juicer. That means there is no need to remove pulp from other parts such as the lid anymore. Due to the round design and smooth surfaces without nooks and crannies, the pulp is easy to reach and the container is much easier to clean.

Specifications

Accessories

Included: Citrus press, Spout

General specifications

Number of speed settings: 2

Product features: Dishwasher safe, Variable speed, Quickclean, Pre-clean

Technical specifications

Capacity jar: 2.5 L

Power: 1000 W

Design

Color: Metallic

