

Masticating juicer

Avance Collection

MicroMasticating technology

White grey

HR1895/81



Unleash all the goodness into your glass

MicroMasticating extracts up to 90%* of the fruit

Philips innovative MicroMasticating technology is designed to open up the cells of your fruits and vegetables to squeeze the maximum out of your ingredients. After juicing, all parts can be rinsed clean in 1 minute thanks to its no sieve design.

Extract all the goodness from fruit and vegetables

- MicroMasticating extracts up to 90%* of the fruit
- Juice all your favourites, including bananas and mangos
- Include leaves, greens and nuts in your drinks
- Pre-clean function squeezes the last drops of juice out

A juicer you can finally rinse clean

- Easily detachable and rinsed clean without any kitchen tool
- Unique no-sieve design for cleaning in under 1 minute
- Innovative drip stop keeps your counter clean

Thoughtfully designed for your kitchen

- Slim juicer with all integrated parts
- Juice directly into your glass
- Inspiring recipe book included
- Detachable parts can be stored in the pulp container

Highlights

MicroMasticating technology



Fruits and vegetables have many thousands of cells that contain juice, vitamins and other vital nutrients. Philips innovative MicroMasticating technology is designed to open up the cells to squeeze the maximum out of your favourite ingredients and will help you to get up to 90%* of your fruits into the glass and not as waste.

Soft fruits to hard vegetables



Make delicious healthy juices from soft fruits and hard vegetables. You can juice all your favourite combinations and use this product even for those special starch ingredients that are normally very difficult to juice such as bananas or mangos.</

Leaves, greens and nuts



Leaves and greens full of fibre are also great ingredients for healthy juices and they can all be processed in this juicer. Wheatgrass, spinach and many others could be an important health-adder to your daily juices with MicroMasticating technology. You can even use certain kind of nuts, such as almonds to prepare almond milk.

Pre-clean function



The pre-clean function is a special programme that squeezes the last drops of juice out of the juicer while cleaning the inside of your product at the same time. This will help you to get the best from your fruits and vegetables and avoid that valuable juice going to waste in the cleaning process.

QuickClean in 1 minute



With an easily detachable design and rimless parts, this juicer can be quickly cleaned using only tap water. Because there are no sharp edges, the fibres or particles of ingredients are rinsed away in seconds.

No-sieve design



Our unique no-sieve design allows the juice to flow seamlessly to your glass, passing through a filter that removes any unwanted parts from the juice and is so easy to clean that you don't need any brushes.

Innovative drip stop



A fully integrated drip stop allows you to stop between juicing sessions and keep your kitchen worktop clean at all times. Simply push the bottom of the juice outlet and without wetting your fingers the juice flow will stop.

Slim design



The optimised, 11 cm-wide design allows you to always keep the juicer on your kitchen worktop, making it ready to juice at any time. It takes very little working space in storage as well as when in use because it is fully integrated, so you don't need any external compartments when juicing.

Directly into your glass



Juicing directly into the glass allows you to tailor each glass to the taste of your family members, to avoid using and having to clean unnecessary parts and keeps your kitchen worktop clear.

Specifications

Accessories

Included: Jug, Recipe booklet

Country of origin

Made in: China

General specifications

Product features: Dishwasher safe, Non-slip feet, On/off switch, Safety lock, QuickClean

Service

2-year worldwide guarantee

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Technical specifications

Capacity jar: 1 l

Capacity pulp container: 1 l

Cord length: 1 m

Frequency: 50–60 Hz

Power: 200 W

Voltage: 220–240 V

Design

Colour: White grey

Finishing

Material accessories: Metal safety lock

Material jar: Plastic

Material of main body: Plastic

Material waste container: Plastic

