

PHILIPS

Juicer

Avance Collection

QuickClean

1200W

XXL feeding tube

Citrus press



HR1925/20

Fresh juice with the fiber you like

Choose up to 50% extra fiber

FiberBoost technology enables you to choose the texture of juice you prefer, selecting with the switch of a button from a refreshing clear juice to a more creamy juice with up to 50% more fiber.

Choose the texture of juice you prefer

- FiberBoost Technology with up to 50% extra fiber

Clean in 1 minute with QuickClean Technology

- Easy to clean sieve
- Just pour in water for quick pre-cleaning
- Pulp naturally falls into one container
- Dripstop for clean kitchen counter

Fresh juice at your convenience

- XXL feeding tube (80mm)
- Powerful 1200W motor
- More silent



Highlights

FiberBoost technology



FiberBoost technology enables you to choose the texture of juice you prefer, selecting with the switch of a button from a refreshing clear juice to a more creamy juice with up to 50% more fiber. The unique combination of smartly controlled constant speeds with unique sieve design allows more or less fiber in your juice, so that everyone can enjoy their favorite.

Easy to clean sieve




Thanks to the polished sieve it is very easy to clean up away leftovers with a kitchen sponge.

More silent



The new motor has a lower noise and vibration which make the overall juicing experience more silent.

Pre-clean



Philips' unique pre-clean function allows you to quickly rinse clean your juicer between different juices or after juicing. By pouring water into the pusher, you can create a water fountain rinsing away unwanted leftovers.

Pulp in one place



Due to the round shape without nooks and crannies the leftovers is collected in the pulp container.

Dripstop



The integrated drip stop allows you to stop between juicer sessions keeping your counter top spotless. Activate the drip stop by simply turning the spout.

XXL feeding tube



Save time and start juicing faster. You no longer need to cut up most fruit and vegetables to fit this juicer machine. Just pop it all into the 80mm XXL feeding tube, and enjoy a boost of nutrition every day.

Powerful 1200W motor

Juice the toughest fruits and vegetables effortlessly with the strong 1200W motor.



IF DESIGN AWARD 2017

IF award-winning products and projects, concepts and more, selected by the top names in design. Each year, iF International Forum Design GmbH organizes one of the world's most celebrated and valued design competitions: the iF DESIGN AWARD. Recognized as a symbol of design excellence around the world, the iF DESIGN AWARD welcomes over 5,000 submissions from 70 countries every year.

Specifications

Accessories

Included: Citrus press, Jug, Recipe booklet

Country of origin

Made in: China

General specifications

Number of speed settings: 2

Product features: Dishwasher safe, Integrated cord storage, Non-slip feet, Quickclean

Service

2-year worldwide guarantee

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Technical specifications

Capacity jar: 1 L

Capacity pulp container: 2.1 L

Cord length: 1 m

Power: 1200 W

Voltage: 220-240 V

Weight and dimensions

Dimensions of packaging (LxWxH): 550 x 320 x 430 mm

Dimensions of product (LxWxH): 296 x 250 x

432 mm

Feeding tube diameter: 80 mm

Weight incl. packaging: 5.4 kg

Design

Color: Metallic

Finishing

Material jug: SAN

Material of main body: Metal

