

# PHILIPS

## MicroMasticating Juicer

### Avance Collection

Up to 90% extraction

Quick clean, in 60 sec

Slim Design

2 juice thicknesses possible



HR1946/70



## Unleash all the goodness into your glass MicroMasticating extracts up to 90%\* of the fruit

Philips' innovative MicroMasticating technology is designed to open up the cells of fruits and vegetables to squeeze the maximum goodness out. Thanks to the large feeding tube on our MicroMasticating Juicer, food doesn't need to be finely chopped, saving you preparation time. After juicing, all parts can be rinsed clean.

### Extract all the goodness from fruit and vegetables

- MicroMasticating extracts up to 90%\* of the fruit
- Juice all your favourites, including bananas and mangos
- Include leaves, greens and nuts in your drinks
- Pre-clean function squeezes the last drops of juice out

### A juicer you can finally rinse clean

- Less preparation with 2 x larger feeding tube
- Easily detachable and rinsed clean without any kitchen tool
- Unique no-sieve design for cleaning in under 1 minute
- Innovative drip stop keeps your counter clean

### Thoughtfully designed for your kitchen

- Slim juicer with all integrated parts
- Juice directly into your glass
- Inspiring recipe book included
- Detachable parts can be stored in the pulp container

# Highlights

## MicroMasticating technology



Fruits and vegetables have many thousands of cells that contain juice, vitamins and other vital nutrients. Philips innovative MicroMasticating technology is designed to open up the cells to squeeze the maximum goodness out of your favourite ingredients, helping you get up to 90%\* of your fruit and vegetable ingredients into the glass.

## Soft fruits to hard vegetables



Make delicious healthy juices from soft fruits and hard vegetables. You can juice all your favourite combinations and use this product even for those special starch ingredients that are normally very difficult to juice such as bananas or mangos.</p>
</div>

## Leaves, greens and nuts

Leaves and greens full of fibre are also great ingredients for healthy juices and they can all be processed in this juicer. Wheatgrass, spinach and many others could be an important health-adder to your daily juices

with MicroMasticating technology. You can even use certain kind of nuts, such as almonds to prepare almond milk.

## Pre-clean function

The pre-clean function is a special programme that squeezes the last drops of juice out of the juicer while cleaning the inside of your product at the same time. This will help you to get the best from your fruits and vegetables and avoid that valuable juice going to waste in the cleaning process.

## QuickClean in 1 minute

With an easily detachable design and rimless parts, this juicer can be quickly cleaned using only tap water. Because there are no sharp edges, the fibres or particles of ingredients are rinsed away in seconds.

## No-sieve design

Our unique no-sieve design allows the juice to flow seamlessly to your glass, passing through a filter that removes any unwanted parts from the juice and is so easy to clean that you don't need any brushes.

## Innovative drip stop

A fully integrated drip stop allows you to stop between juicing sessions and keep your kitchen worktop clean at all times. Simply push the bottom of the juice outlet and, without dripping on your fingers, the juice flow will stop.

## Slim design

The optimised, 11 cm-wide design takes up so little space on your kitchen worktop that you can leave it out, making it ready for use at any time. It also takes up very little storage space when not in use because it is fully integrated, so you don't need any external compartments when juicing.

## Directly into your glass

Juicing directly into the glass allows you to customise every juice to taste and avoid cleaning unnecessary parts.

---

## IF DESIGN AWARD

IF award-winning products and projects, concepts and more, selected by the top names in design. Each year, iF International Forum Design GmbH organises one of the world's most celebrated and valued design competitions: the iF DESIGN AWARD. Recognised as a symbol of design excellence around the world, the iF DESIGN AWARD welcomes over 5000 submissions from 70 countries every year.

---

# Specifications

## Accessories

Included: Filter, Recipe booklet

## Country of origin

Made in: China

## General specifications

Product features: Dishwasher safe, Non-slip feet, On/off switch, Safety lock, QuickClean

## Service

2-year worldwide guarantee

## Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

## Technical specifications

Capacity pulp container: 1 l

Cord length: 1 m

Frequency: 50–60 Hz

Power: 200 W

Voltage: 220–240 V

RPM: 300 RPM

## Design

Colour: Black

## Finishing

Material accessories: Metal safety lock

Material of main body: Plastic

Material waste container: Plastic

