

# PHILIPS

## Blender

750 W

2 liter



HR2094



### Extra power for superior blending and crushing 750 W motor with speed precision

The Philips blender in anodised aluminium features a 750 W engine, which can handle just about anything – from fruit and vegetables to ice. Its multi-speed function will blend, crush and cut to almost any consistency you want.

#### Easy to clean

- Detachable blade unit for easy cleaning

#### Choose the exact speed you need

- Variable speed control with illuminated display

#### Make the perfect smoothie and crush ice instantly

- Ice crush button
- Filter for clear juice
- Long-lasting serrated blades

#### Smell and scratch resistant

- High quality glass jar

#### Powerful

- 750 Watt Motor

# Highlights

## 750 Watt Motor



Effortlessly mix, crush and chop all your ingredients with this powerful 750W motor.

## Detachable blade



Clean easily and effectively by removing the blade from the jar.

## High quality glass jar

Scratches and smells are prevented by this high quality glass jar.

## Ice crush button



Crush ice easily with the touch of a button.

## Variable speed control with illuminated display



Set the blender to the speed you want with this unique control knob.

## Filter for clear juice



Keep seeds and pips out of your juice with this convenient filter.

## Long-lasting serrated blades



Crush and blend to perfection with these long-lasting, ultra-sharp blades.

# Specifications

## Design specifications

Color(s): White, blue and apricot  
Material blender jar: Glass  
Material housing: Anodized Aluminium  
Material knife: Stainless steel

## General specifications

Integrated cord storage  
Speeds: Variable + pulse

## Technical specifications

Capacity blender jar: 2 l  
Frequency: 50/60 Hz  
Power: 750 W  
Voltage: 220-240 V

## Accessories

Filter

