

PHILIPS

Blender

600W

2 L Plastic Jar

5 speed and pulse

HR2118/01



More than a blender

Blend super smoothie, tasty soups and healthy juice

The Philips blender is your gateway to serving variety every day. Make your own fresh juices. Blend homemade soups or create nutritional smoothies. With 600W, multiple speed settings and a fruit filter the possibilities are unlimited

For perfect smoothie and food preparation

- Powerful 600W motor
- Multiple speeds
- Ultra-sharp, long lasting serrated blades

Smart accessories

- Multi mill accessory
- Convenient filter accessory
- Chopper for chopping various ingredients

Easy to clean

- Detachable blade unit for easy cleaning
- Easy cleaning soft touch panel
- Quick clean button
- All parts dishwasher safe, except for main unit

Quality guaranteed

- 2 year guarantee


Highlights

600W motor

600W

Strong 600W motor for blending and mixing easily.

Multiple speeds



Blend at different speeds and to different degrees with a choice of settings.

Ultra-sharp serrated blades



Crush and blend to perfection with these ultra-sharp, long-lasting serrated blades.

Multi mill accessory



Multi mill for grinding and chopping hard and soft ingredients.

Detachable blade



Clean easily and effectively by removing the blade from the jar.

Filter accessory



Keep seeds and pips out of your juice with this convenient filter.

Chopper



The Philips blender accessory complete your blender. This chopper chops vegetables like onions, herbs, nuts and meat into fine pieces.

Quick clean button



One touch quick clean button to clean the jar and blade effectively.

Soft touch panel



Clean easily wipe out the surface.

Dishwasher safe



All parts dishwasher safe, except for main unit

2 year guarantee



With 2 years world-wide warrantee.

Specifications

Design specifications

Material housing: Polypropylene (PP)

Material blade: Stainless steel

Material blender jar: SAN

Color(s): White

General specifications

Non-slip feet

Integrated cord storage

Speed setting: 5 and pulse

Technical specifications

Power: 600 W

Effective jar capacity: 1.5 L

Frequency: 50/60 Hz

Capacity jar: 2 L

Voltage: 220-240 V

Cord length: 0.85 m

Accessories

Chopper

Filter

Mill

