

PHILIPS

Blender

Viva Collection

600 W

2 L Plastic Jar

Multiple speeds and pulse

ProBlend 5



ProBlend 5

HR2162/91



Silkier green smoothie in seconds

Fewer chunks with the ProBlend 5 technology*

This Philips Viva Collection blender offers a 600-W motor, 2-l jar and ProBlend 5 blade combined to create perfect end results for your smoothie and food preparation. It makes your tough blending easy!

Supreme blending performance

- Strong 600-W motor
- ProBlend 5 star blade for effective blending and mixing
- Large break-resistant jar for smoothies you can share
- Multiple speeds for soft and hard ingredients

Easy to use

- Over-moulded knob for easy grip
- Pulse for mixing and blending
- Water level indicator and handle for easy use

Easy to clean

- All parts are dishwasher safe

Quality guaranteed

- 2-year worldwide warranty



asimpleswitch.com

Highlights

600-W motor

600W

Strong 600-W motor for blending and mixing easily.

ProBlend 5




ProBlend 5 star blade for effective blending and mixing.

Large break-resistant jar




Avoid breakages with this reinforced plastic jar. The large 2 litre jar has a working capacity of 1.5 litres for smoothies you can share.

Multiple speeds



Blend at different speeds and to different degrees with a choice of settings.

Over-moulded knob



Over-moulded knob for easy grip and better speed control.

Pulse for mixing and blending



You can use "Pulse" mode to control blending degree and time conveniently.

Water level indicator



Water level indicator and handle for easy use and pouring.

All parts are dishwasher safe



All parts are dishwasher safe

2-year worldwide warranty



2-year worldwide warranty



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Design specifications

Material housing: Polypropylene (PP)

Material blade: Stainless steel

Material blender jar: Styrene Acrylonitrile (SAN)

Colour(s): Black and Cashmere Grey

General specifications

Cord storage

Non-slip feet

Speed setting: 2 and pulse

Technical specifications

Power: 600 W

Effective jar capacity: 1.5 l

Frequency: 50/60 Hz

Voltage: 220–240 V

Cord length: 1.0 m

Max. Jar Capacity: 2 l

