



Philips Avance Collection
Blender

900 W

2 L glass jar
with spatula
ProBlend 6



HR2195/01

Best blending, leaves no bits

ProBlend 6 technology for up to 50% finer result*

The Philips blender with ProBlend 6 and 900 W motor can handle just about anything — from fruits/vegetables to ice. Its multi-speed function will blend, crush and cut for perfectly smooth blending and any consistency you want.

Choose the exact speed you need

- Variable speed control with illuminated display
- Programmed ice-crushing function
- One-touch pulse and quiet mode

Make perfect smoothies and crush ice instantly

- Unique off-centre jar design to mix ingredients efficiently
- Max 2-l (with food 1.5-l) high-quality glass jar
- ProBlend 6 star blade for blending and cutting effectively
- Powerful 900-W motor

Ease of use

- Spatula for mixing ingredients easily

Easy to use and clean

- Dishwasher safe, except for the main unit and blade assembly
- Easy cleaning with detachable blade

Blender
900 W 2 L glass jar, with spatula, ProBlend 6

Highlights

Variable speed control with illuminated display



Set the blender to the speed you want with this unique control knob.

Detachable blade unit



Easy cleaning with detachable blade

Programmed ice-crush function



Motor will operate pre-programmed sequence to crush ice easily at the touch of a button

Spatula



The handy spatula of the Philips blender ensures safe stirring while blending the ingredients.

Unique jar

Blade positioned off-centre in the jar will create turbulence and mix ingredients in the most effective way.

Dishwasher safe



All parts are dishwasher safe, except for the main unit and blade assembly.

2 L glass jar



The 2-l jar is made of high-quality glass, which is scratch-proof, and makes it possible to process hot ingredients.

HR2195/01

ProBlend 6 star blade



Philips blender with innovative ProBlend 6 technology for blending fruits, cutting vegetables and crushing ice in the most effective way.

Pulse and quiet mode



Pulse button to control the operation and quiet mode that will run at low speed causing a lower decibel level.

900 W motor

This Philips blender has a strong 900 W motor for blending, mixing and crushing effectively.



Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Blender
900 W 2 L glass jar, with spatula, ProBlend 6

HR2195/01

Specifications

General specifications

- Product features: Cord storage, Non-slip feet

Technical specifications

- Capacity jar: 1.5 l
- Cord length: 1 m
- Frequency: 50 - 60 Hz
- Power: 900 W
- Voltage: 220 - 240 V

Design

- Colour: Stainless steel

Finishing

- Material blade: Stainless steel
- Material jar: Glass
- Material of main body: PP



Issue date 2018-02-06

Version: 2.0.1

EAN: 08 71010 37239 81

© 2018 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Compare to Philips' number one blender HR2094