

PHILIPS

Blender

Avance Collection

900 W

2 L glass jar

with spatula

ProBlend 6

HR2196/38



Best blending, leaves no bits

ProBlend 6 technology for up to 50% finer result*

The Philips blender with ProBlend 6 and 900W motor can handle just about anything – from fruits/vegetables to ice. Its multi-speed function will blend, crush and cut for perfectly smooth blending and any consistency you want.

Choose the exact speed you need

- Variable speed control with illuminated display
- One touch pulse and smoothie button
- Programmed ice crushing function

Make perfect smoothies and crush ice instantly

- Unique off-center jar design to mix ingredients efficiently
- Max 2 L (with food 1.5 L) high quality glass jar
- ProBlend 6 star blade for blending and cutting effectively
- Powerful 900 W motor

Ease of use

- Spatula for mixing ingredients easily

Easy to use and clean

- Dishwasher safe, except for the main unit and blade assembly
- Easy cleaning with detachable blade

Highlights

Unique jar

Blade positioned off-center in the jar will create turbulence and mixing ingredients in the most effective way.

2 L glass jar



The 2 L jar is made of high quality glass which is scratch proof, and allows to process hot ingredients.

Variable speed control with illuminated display



Set the blender to the speed you want with this unique control knob.

Programmed ice crush function



Motor will operate pre-programmed sequence to crush ice easily with the touch of a button

Pulse and smoothie button



Pulse button to control the operation whatever you want and smoothie button for making the best tasting smoothie by pressing once.

Spatula



The handy spatula of the Philips blender ensures a safe stirring while blending the ingredients.

Detachable blade unit



Easy cleaning with detachable blade

Dishwasher safe



All parts are dishwasher safe, except for the main unit and blade assembly.

ProBlend 6 star blade



Philips blender with innovative ProBlend 6 technology for blending fruits, cutting vegetables and crushing ice with the most effective way.

900 W motor

This Philips blender has a strong 900 W motor for blending, mixing and crushing effectively.

Specifications

General specifications

Product features: Cord storage, Non-slip feet, Pulse, Variable speed

Technical specifications

Capacity jar: 2 L
Cord length: 1 m
Frequency: 50 - 60 Hz
Power: 900 W
Voltage: 220 - 240 V

Design

Color: Burgundy red

Finishing

Material blade: Stainless steel
Material jar: Glass
Material of main body: PP

