

PHILIPS

Pasta maker

Avance Collection

500g

200W

Various types of pasta

HR2354



Enjoy fresh homemade pasta in 10 minutes

Auto-weighing function ensures consistent result

Fresh flavorful homemade pasta has never been easier. With 1600 lb extrusion force and auto-weighing function, the Philips pasta maker can make 300 gram of pasta with perfect texture in just 10 minutes, and it is a fully automatic solution

Fresh and flavorful pasta & noodle

- Makes 300 gram of pasta or noodle in just 10 minutes

Consistent and great result.

- Built-in auto-weighing function
- Unique shaping discs to create various types of pasta

Enjoy full convenience of making pasta

- Automatic mixing, kneading and extruding

Various type and flavor of pasta & noodle

- Adding different ingredients to personalize the flavor
- A free recipe book with over 20 different pasta dishes

Highlights

Automatic process



After choosing program and pressing start button, the machine automatically mixes, kneads and extrudes in one go.

Personalized taste



By using different types of flour and adding different ingredients like eggs, herbs or spinach and carrot juice, you can make various types and flavors of pasta or noodle.

Auto-weighing



The unique designed built-in auto-weighing function weighs the flour and indicates the correct amount of liquid automatically, making the whole process easier and more convenient than ever.

Unique shaping discs



The pasta maker comes with various shaping discs including Penne, Spaghetti, Fettuccine, Angel hair, Pappardelle/thick flat, Lasagne, Ravioli /dumpling. You can easily bring variety to the table.

Recipe book



Accompanying with the machine there is a colorful recipe book provides ingredient list for different types or flavors of pasta and recipe for over 20 pasta / noodle dishes

Powerful and fast extrusion



With advanced engineering and robust material and build of the machine, the Philips Pasta and noodle maker can exert 1600 lb force on the dough during extrusion, which not only enables a fast making process in just 10 minutes, but also guarantees perfect texture and taste of the pasta or noodle.

Specifications

Accessories

Included: Cleaning tool, Measuring cup, Recipe booklet

Country of origin

Made in: China

General specifications

Number of shaping mouths: 6

Prefix programs: 2

Product features: Detachable shaft, LED display, Non-slip feet, Ready signal, Safety lock

Technical specifications

Cord length: 1.2 m

Frequency: 60 Hz

Power: 200 W

Voltage: 220-240 V

Weight and dimensions

Dimensions of product (LxWxH): 343 x 215 x 315 mm

Weight incl. packaging: 10.2 kg

Weight of product: 6.9 kg

Design

Color: Cashmere grey

Color of control panel: Silver

Finishing

Material accessories: POM

Material of main body: Plastic

