

# PHILIPS

Noodle Maker

Avance Collection

500g

200W

HR2355/02



## Enjoy freshly homemade noodles with minimum effort

### Automatic solution to make various types of noodle

With 360 degree extrusion technology, it allows you to enjoy fresh and tasty noodle within 15 minutes! Add in nutritious ingredients like egg, spinach, and carrot juice to create healthy and worry-free homemade noodles for your family!

#### Quick and easy noodle making

- Automatic noodle making
- Quick noodle making - in 15 minutes

#### Noodle in all kinds of shapes

- Various shaping mouths to create different types of noodles

#### Safe and authentic noodles

- Create authentic noodles with all kinds of fresh ingredients

#### Food grade material (BPA Free)

- Food grade material (BPA Free) for all food contacting part

#### Easy to use

- Smart drawer design for shaping mouths storage
- Special cleaning tool for shaping mouths
- LED display to show working process



# Highlights

## Powerful extrusion technology

Powerful kneading and extruding bar not only facilitates automatic noodle making but also provides thorough kneading and quick extruding

## Quick noodle making



Kneading and extruding will be finished in only 15 minutes: yields around 500g of noodle

## Various shaping mouths



Allow you to make 4 types of noodles: round thin noodle, round thick noodle, flat thin noodle, and flat thick noodle

## Safe and authentic noodles

Add in fresh ingredients like egg, spinach juice, or carrot juice to create healthy and nutritious noodles. It is 100% safe because you have the full control

## Food grade material (BPA free)



All food contacting part is made with food grade materials (BPA Free) so you can use with peace of mind

## Smart storage space



Smart drawer to keep all the shaping mouths in one place

## Special cleaning tool



Special cleaning tool to clean the shaping mouths more easily

## LED display



LED display to show working process, let you feel better in control.



## IF DESIGN AWARD

iF award-winning products and projects, concepts and more, selected by the top names in design now aEach year, iF International Forum Design GmbH organizes one of the world's most celebrated and valued design competitions: the iF DESIGN AWARD. Recognized as a symbol of design excellence around the world, the iF DESIGN AWARD welcomes over 5,000 submissions from 70 countries every year.

# Specifications

**Accessories**

**Included:** Cleaning tool, Measuring cup

**Technical specifications**

**Power:** 200 W

**Frequency:** 20 Hz

**Cord length:** 1.2 m

**Country of origin**

Made in: China

**Design**

**Color:** White & purple

**Finishing**

**Material accessories:** Plastic

**Material of main body:** Plastic

**General specifications**

**Product features:** LED display

**Weight and dimensions**

**Weight of product:** 7.5 kg

