

PHILIPS

Pasta and noodle
maker

Premium collection

500g

200W



HR2357/08



Enjoy fresh homemade pasta & noodle in 15 minutes

Automatic solution to make various types of pasta

Fresh and flavorful homemade pasta and noodle have never been easier. With 1600 lb extrusion force, it can make 1 pound of pasta or noodle with perfect texture in just 15 minutes, and it is a fully automatic solution!

Fresh and flavorful pasta & noodle

- Makes half pound of pasta in just 10 minutes

Various type and flavor of pasta & noodle

- A free recipe book with over 20 different dishes
- Unique shaping discs to create various types of pasta/noodle
- Adding different ingredients to personalize the flavor

Enjoy full convenience of making pasta

- Automatic mixing, kneading and extruding

Save cleaning time and effort

- Specially designed cleaning tool for easy one-push cleaning
- Smart drawer design for shaping discs storage

Highlights

Recipe book

Accompanying the machine is a colorful recipe book which provides ingredient lists for 24 different types or flavors of pasta and recipes for over 20 pasta / noodle dishes.

Various shaping discs

With the machine there are 4 default shaping discs for Spaghetti, Penne, Fettuccini and Lasagna. More shaping discs will come as additional accessories for different types of noodle and pasta.

Powerful and fast extrusion

With advanced engineering and robust material and build of the machine, the Philips Pasta Maker can exert 1600 lb force on the dough during extrusion, which not only enables a fast making process in just 10 minutes, but also guarantees perfect texture and taste of the pasta.

Automatic process

After choosing program and pressing start button, the machine automatically mixes, kneads and extrudes in one go.

One-push cleaning tool

There are specially designed cleaning tool matching the shaping discs (Spaghetti and Fettuccini) that makes cleaning an easy one-push job.

Personalized taste

By using different types of flour and adding different ingredients like eggs, herbs or spinach and carrot juice, you can make various types and flavors of pasta or noodle.

Storage

At the bottom of the Pasta and noodle maker there is a storage drawer where you can easily store the shaping discs and cleaning tools.

Specifications

Accessories

Included: Cleaning tool, Measuring cup, Recipe booklet

Country of origin

Made in: China

General specifications

Number of shaping mouths: 4

Prefix programs: 2

Product features: Automatic shut-off, Detachable shaft, LED display, Non-slip feet, On/off switch, Preset cooking function, Ready signal, Safety lock, Power-on light

Service

2-year worldwide guarantee

Technical specifications

Cord length: 1.2 m

Frequency: 50 Hz

Power: 200 W

Voltage: 220 - 240 V

Weight and dimensions

Dimensions of packaging (LxWxH): L405 x W305 x H340 mm

Dimensions of product (LxWxH): L343 x W215 x H300 mm

Weight incl. packaging: 8.9 kg

Weight of product: 7.5 kg

Design

Color: Champagne

Color of control panel: Silver

Finishing

Material accessories: Plastic

Material bar: AL+PTFE Coating

Material of main body: Plastic

