

Pasta maker

Avance Collection

1 pound pasta

in 15 mins

Various types of pasta



HR2358/05



Enjoy fresh homemade pasta in 15 minutes Auto-weighing function ensures great result

Fresh and flavorful homemade pasta has never been easier. With 1600 lb extrusion force and auto-weighing function, the Philips pasta maker can make 1 pound of pasta within 15 minutes, and it is a fully automatic solution!

Fresh and flavorful pasta & noodle

- Makes a pound of pasta or noodle in just 15 minutes

Consistent and great result.

- Built-in auto-weighing function
- Unique shaping discs

Enjoy full convenience of making pasta

- Automatic mixing, kneading and extruding

Various type and flavor of pasta & noodle

- Adding different ingredients to personalize the flavor
- A free recipe book with over 20 different dishes



Highlights

Powerful and fast extrusion



With advanced engineering and robust material and build of the machine, the Philips Pasta and noodle maker can exert 1600 lb force on the dough during extrusion, which not only enables a fast making process in just 15 minutes, but also guarantees perfect texture and taste of the pasta or noodle.

Auto-weighing



The unique designed built-in auto-weighing function weighs the flour and indicates the correct amount of liquid automatically, making the whole process easier and more convenient than ever.

Unique shaping discs



The pasta maker comes with 8 shaping discs including Penne, Spaghetti, Fettuccine, Lasagne/dumpling, Angel hair, Thick spaghetti, Tagliatelle and Pappardelle. You can easily bring variety to the table.

Automatic process



After choosing program and pressing start button, the machine automatically mixes, kneads and extrudes in one go.

Personalized taste



By using different types of flour and adding different ingredients like eggs, herbs or spinach and carrot juice, you can make various types and flavors of pasta or noodle.

Recipe book



Accompanying the machine is a colorful recipe book which provides ingredient lists for 24 different types or flavors of pasta and recipes for over 20 pasta / noodle dishes.

Specifications

Accessories

Included: Cleaning tool, Measuring cup, Recipe booklet

Technical specifications

Power: 200 W

Cord length: 1.2 m

Frequency: 60 Hz

Voltage: 120 V

Weight and dimensions

Dimensions of product (LxWxH): 343 x 215 x 315 mm

Weight of product: 6.9 kg

Weight incl. packaging: 10.2 kg

Country of origin

Made in: China

Design

Color of control panel: Silver

Color: Cashmere grey

Finishing

Material accessories: POM

Material of main body: Plastic

General specifications

Number of shaping mouths: 8

Prefix programs: 2

Product features: LED display



IF DESIGN AWARD

iF award-winning products and projects, concepts and more, selected by the top names in design now aEach year, iF International Forum Design GmbH organizes one of the world's most celebrated and valued design competitions: the iF DESIGN AWARD. Recognized as a symbol of design excellence around the world, the iF DESIGN AWARD welcomes over 5,000 submissions from 70 countries every year.

