

# Food preparation range 2001



HR 1453 HR 1455 HR 1456 HR 1560 HR 1561 HR 1570 HR 1571 HR 1565 HR 1554 HR 1555

## MIXERS

	HR1453 <sup>1)</sup> Comfort	HR1455 <sup>2)</sup> Comfort	HR1456 <sup>2)</sup> Comfort	HR1560 Cucina	HR1561 Cucina	HR1570 Essence	HR1571 Essence	HR1565 <sup>3)</sup> Cucina	HR1554 <sup>4)</sup> Cucina	HR1555 <sup>4)</sup> Creamix
<b>Features</b>										
Wattage (W)	175	175	175	220	220	240	240	220	190	190
Speed	3 + turbo	5 + turbo	5 + turbo	3 + turbo	3 + turbo	3 + turbo	3 + turbo	3 + turbo	3 + pulse	3 + pulse
Eject function	●	●	●	●	●	●	●	●	●	●
FlexiMix function	-	-	-	-	-	●	●	-	-	-
Cordstorage	Clip	Clip	Clip	Suction cap	Suction cap	Suction cap	Suction cap	Suction cap	Clip	Clip
Pictograms	●	●	●	●	●	●	●	●	●	●
<b>Accessories</b>										
Strip beaters	●	●	●	●	●	●	●	●	●	●
Wire beaters	○	○	○	○	○	○	○	-	-	-
Kneading hooks	●	●	●	●	●	●	●	●	●	●
Pureeing accessory	-	-	-	-	-	-	-	-	-	-
Storagebox	-	-	-	-	-	-	-	-	-	-
Driven stand& bowl	-	-	-	-	-	-	-	-	-	-
Non-driven stand& bowl	-	-	-	-	-	-	-	-	-	-
Spatula	-	-	-	-	-	-	-	●	-	● 2 bowls
<b>Logistic data</b>										
Dimensions (mm) (LxWxH)										
-Product	●	●	●	180x90x160	180x90x160	180x95x160	180x95x160	304x172x350	330x120x330	330x120x330
-F-box	185x92x185	185x92x185	185x92x185	224x99x227	203x110x227	224x99x227	203x110x227	368x283x240	330x230x200	330x230x200
-A-box	288x388x209	288x388x209	288x388x209	603x233x251	613x229x251	603x233x251	618x229x251	745x575x264	Foil	Foil
Pieces per A-box	6	6	6	6	6	6	6	4	4	4
Pieces per euro pallet	384	384	384	336	336	336	336	56	96	96
Weight product in packaging (gr)	1200	1200	1200	1408	1560	1450	1660	2500	1500	1800

<sup>1)</sup> Execution for Europe only

<sup>2)</sup> Execution for all regions except for Europe

<sup>3)</sup> Introduction September 2001

<sup>4)</sup> Execution for Latam only

○ = optional



HR1340 HR1350/6" HR1350/32" HR1351 HR1354 HR1355 HR1356 HR1357

## BARBLENDERS

	HR1340 Comfort	HR1350 Cucina	HR1351 Cucina	HR1354 Cucina <sup>1)</sup>	HR1355 Essence	HR1356 Essence	HR1357 Essence
<b>Features</b>							
Wattage (W)	190	250	250	250	300	300	300
Speed	1	1	1	1	1	1	4
Twist & Slice blades	-	●	●	●	●	●	●
Detachable bar	-	●	●	●	●	●	●
Material bar	Plastic	Plastic	Plastic	Plastic	Metal	Metal	Metal
<b>Accessories</b>							
Beaker & lid	-	●	●	●	●	●	●
Wall bracket	-	●	●	●	●	●	●
Chopper	-	-	-	●	-	-	●
Metal whisk	-	-	-	●	-	-	●
Metal filter	-	-	-	●	-	-	●
<b>Logistic data</b>							
Dimensions (LxWxH-mm) and weight (kg)							
Product dimensions	80x70x355	●	●	385x70x70	●	●	385x70x70
Product weight	0.6	●	●	0.65	●	●	0.95
F-box dimensions	80x80x375	144x144x402	310x130x244	480x300x128	210x127x280	310x150x244	480x300x128
F-box weight	0.8	1.2	1.5	2.0	1.5	1.8	2.3
A-box dimensions	383x168x264	447x298x422	635x400x264	529x494x329	495x391x300	635x460x264	529x494x329
A-box weight	5.1	8.5	10.3	9.1	10.3	12.1	10.3
Pieces per A-box	6	6	6	4	6	6	4
Euro pallet dimensions	1200x800x2000	1220x822x1904	1200x800x1967	1200x823x1727	1248x819x1922	1200x800x1967	1200x823x1727
Euro pallet weight	515	302.0	246.3	151.5	400.8	199.4	169.5
F-boxes per euro pallet	588	192	126	60	216	84	60
A-boxes per euro pallet	98	32	21	15	36	14	15
Layer per euro pallet	7	4	7	3	6	7	3
A-boxes per layer	14	8	3	5	6	2	5

\* very blue

\*\* golden green



Beaker & Lid Wall bracket Chopper Metal whisk Metal filter



HR 2303 HR 2304 HR 2305

## ICE CREAM MAKERS

	HR 2303 Comfort	HR 2304 Comfort	HR 2305 Cucina
<b>Features</b>			
Wattage (W)	20	20	30
Capacity (L)	0.8	1.0	1.0/1.2
Freezing time cooling elem.	18 hours	18 hours	18 hours
Cooling element (mm)	95x Ø 196 basket	65x Ø 170 disc	65x Ø 170 disc
Preparation time (min.)	20-40	30-50	20-50
Recipebook	-	●	●
LED procesready signal	-	-	●
<b>Logistic data</b>			
Dimensions mm (LxWxH)			
<b>Product</b>	280x220x220	280x220x260	250x230x270
Weight product (kg)	1.85 kg	1.9 kg	3.4 kg
<b>F-box</b>	290x290x260	290x290x300	290x290x350
Weight product in F-box (kg)	2.4	3.5	4.3
<b>A-box</b>	600x300x290	600x300x330	600x300x380
Pcs	2	2	2
Weight A-box (kg)	5.1	7.3	8.9
<b>Euro pallet</b>	1200x800x2180	1200x800x2090	1200x800x2020
Layers	7	6	5
A-boxes per layer	4	4	4
Total pcs	56	48	40
Total weight (kg)	157	189	192



HR 2737 HR 2791 HR 2792 HR 2752 HR 2794 HR 2795 HR 2796



HR 1840 HR 1841 HR 2825 HR 2826 HR 2828



HR 1700 HR 2845 HR 1730 HR 1764 HR 1774 HR 1784



HR 2385 HR 2387/6 HR 2388/0 HR 2389/7

**CITRUS PRESSES**

	HR 2737 Comfort	HR 2791 Cucina	HR2792 Cucina	HR 2752 Essence	HR 2794 LATAM version	HR 2795 LATAM version	HR 2796 LATAM version
<b>Features</b>							
Wattage (W)	25	25	25	85	25	25	25
Capacity (L)	0.4	0.6	1.0	Direct flow	1.0	1.0	1.5
Pulp sweeper	-	●	●	●	●	●	●
Cordwinder	●	●	●	●	●	●	●
Dustcover	-	●	●	●	-	●	●
Pulp selector	-	●	●	-	-	-	-
Direct flow	-	-	-	-	-	-	-
Drip stop	-	-	-	●	-	-	-

**Logistic data**

Dimensions mm (LxWxH)	HR 2737	HR 2791	HR2792	HR 2752	HR 2794	HR 2795	HR 2796
Product	208x160x165	215x170x180	230x170x200	220x220x235	220x160x215	220x160x215	240x160x260
Weight product	0.6	0.6	0.7	1.9	0.66	0.76	0.77

**F-box**

Dimensions mm (LxWxH)	HR 2737	HR 2791	HR2792	HR 2752	HR 2794	HR 2795	HR 2796
Product	190x190x175	215x215x230	215x215x260	260x260x280	212x212x250	212x212x250	212x212x280
Weight F-box	0.7	0.9	1.0	2.4	1.0	1.1	1.3

**A-box**

Dimensions mm (LxWxH)	HR 2737	HR 2791	HR2792	HR 2752	HR 2794	HR 2795	HR 2796
Product	390x390x362	660x440x250	440x270x460	540x280x300	660x440x250	660x440x250	660x440x280
Pcs	8	6	4	2	6	6	6
Weight A-box	6.3	5.7	4.7	5.5	6.5	7.2	8.2

**Europallet**

Dimensions mm (LxWxH)	HR 2737	HR 2791	HR2792	HR 2752	HR 2794	HR 2795	HR 2796
Product	1200x800x1950	1200x800x2220	1200x810x1980	1200x800x2060	1250x800x1750	1250x800x1750	1250x800x1680
Layers	5	8	4	6	7	7	8
A-boxes per layer	6	2	6	6	2	2	3
Total pcs	240	96	96	72	84	84	108
Total weight (kg)	205	105	127	212	128	129	164

**JUICE EXTRACTORS**

	HR 1840 Juice & Co	HR 1841 Juice & Co	HR 2825	HR 2826	HR2828 Vito
<b>Features</b>					
Wattage (W)	300	300	220	220	250
Speeds	2 + pulse	2 + pulse	1	1	1
Safety system	●	●	●	●	●
Cordstorage	●	●	-	-	●
<b>Accessories</b>					
Juice cup	●	●	-	●	-
Blender	●	●	-	-	-
Mill	-	-	-	-	-
Cleaning brush	●	●	-	-	●

**Logistic data**

Dimensions mm (LxWxH)	HR 1840	HR 1841	HR 2825	HR 2826	HR2828
Product	184x264x296 (juicer)	184x264x296 (juicer)	205x140x240	205x140x240	283x198x268
	181x212x409 (blender)	181x212x280 (blender)			
		181x212x280 (mill)			
Weight product (kg)	2.8	3.08			2.3

**F-box**

Dimensions mm (LxWxH)	HR 1840	HR 1841	HR 2825	HR 2826	HR2828
Product	479x214x335	415x370x335	270x240x260	342x240x272	280x280x289
Weight F-box (kg)	3.8	4.2	2.1	2.3	2.9

**A-box**

Dimensions mm (LxWxH)	HR 1840	HR 1841	HR 2825	HR 2826	HR2828
Product	495x465x705	430x385x700	560x510x280	705x505x300	304x580x615
Pcs	4	2	4	4	4
Weight A-box (kg)	16.6	10.4	12.4	16.8	12.62

**Europallet**

Dimensions mm (LxWxH)	HR 1840	HR 1841	HR 2825	HR 2826	HR2828
Product	1200x800x1900				
Layers	3				
A-boxes per layer	6				
Total pcs	72				
Total weight (kg)	223.2				227.2

**BLENDERS**

	HR 1700-17 <sup>1</sup> Twist	HR 2845	HR 1730 Twister	HR 1764	HR 1774	HR 1784
<b>Features</b>						
Wattage	250	400	400	400/500	400/500	400/500
Speed	1	3 + P (slide)	3 + P	3 + P (push)	5 + P (push)	5 electronic
Capacity (total)	1.25	2	2	2	2	2
Cordstorage	●	●	●	●	●	●
Safety cap	-	●	●	●	●	●
Volume indicator	●	●	●	●	●	●
Glass jar	-	-	Optional	-	-	-
Sieve in lid	●	-	●	●	●	●
Quick Clean button	-	-	●	●	●	●

**Accessories**

	HR 2945	HR 2924	HR 2940	Optional	Optional	Optional
Mill	-	HR 2924	HR 2940	Optional	Optional	Optional
Chopper	-	HR 2926	HR 2939	Optional	Optional	Optional
Fruit filter	HR 2938	HR 2849	HR 2938	●	●	●

**Logistic data**

Dimensions 3 (mm) (LxWxH)	HR 1700	HR 1704	HR 2805	HR 1764	HR 1774	HR 1784
- product	140x170x360	140x170x360	215x170x385	205x215x395	205x215x395	205x215x395
- single packaging	292x192x224	323x192x224	284x224x272	336x196x245	336x196x245	336x196x245
- transport packaging	592x392x229 <sup>1</sup>	654x392x229 <sup>1</sup>	654x392x229 <sup>1</sup>	339x338x472 <sup>2</sup>	339x338x472 <sup>2</sup>	339x338x472 <sup>2</sup>
	270x560x395	286x606x466	339x338x472			
Pieces per unit	4	4	4	4	4	4
Pallet	112	84	64	72	72	72
Weight product in packaging	1.9kg	2.0kg	3.8kg	2.3kg	2.3kg	2.3kg

<sup>1</sup> HR 1710 2 speeds. <sup>2</sup> Dimensions might be different for Asia. <sup>3</sup> Shrink.



fruitfilter chopper mill

HR 17x0= with out accessories  
 HR 17x1= mill  
 HR 17x2= chopper  
 HR 17x3= chopper + mill  
 HR 17x4= fruit filter  
 HR 17x7= fruit filter + mill  
 HR 17x8= fruit filter + chopper  
 HR 17x9= fruit filter + chopper + mill

**ELECTRONIC KITCHEN SCALES**

	HR 2385 Comfort	HR 2387/6 Cucina	HR 2388/0 Essence	HR 2389/7 Metal
<b>Features</b>				
Power supply	9 V battery	9 V battery	9 V battery	9 V battery
Capacity	max. 5 kg	max. 3 kg	max. 5 kg	max. 5 kg
Division	1 gram	2 gram	1 gram	1 gram

**Logistic data**

Product	HR 2385	HR 2387/6	HR 2388/0	HR 2389/7
Dimensions (LxWxH)	210 x185x42 mm	∅ 220x40 mm	245x200x40 mm	245x200x40 mm
Weight	0,53 kg	0,43 kg	0,50 kg	0,725 kg

**F-box :**

Dimensions (LxWxH)	HR 2385	HR 2387/6	HR 2388/0	HR 2389/7
Product	240x70x250 mm	237x70x284 mm	237x70x314 mm	237x70x314 mm
Weight	0,70 kg	0,58 kg	0,68 kg	0,90 kg

**A-box:**

Dimensions (LxWxH)	HR 2385	HR 2387/6	HR 2388/0	HR 2389/7
Product	356x230x267 mm	360x260x260 mm	360x290x260mm	360x290x260 mm
Weight	3,75 kg	3,1 kg	3,7 kg	4,8 kg
pcs. per A-box	5	5	5	5

**EU-pallet:**

Dimensions (LxWxH)	HR 2385	HR 2387/6	HR 2388/0	HR 2389/7
Product	1200x800x1200 mm	1200x800x1180 mm	1200x800x1180 mm	1200x800x1180 mm
A-boxes per layer	10	9	8	8
A-boxes per pallet	40	36	32	32
Appliance per pallet	200	180	160	160
Total weight (excl. pallet)	150 kg	112 kg	118 kg	154 kg