

Highlights

2 speed settings and pulse



For best results, use the low speed setting (speed 1) to whip cream, beat eggs, create pastries and bread dough. The higher speed setting (speed 2) is well suited to chop onions and meats, blend soups and smoothies or shred, slice, grate or rasp vegetables.

40% larger feeding tube



The new Philips Daily collection Food Processor comes with a feeding tube which is 40% larger than the previous HR7625 model, saving precutting time of fruits and vegetables

Stainless steel disc inserts



Simply select the right stainless steel disc insert to prepare your favorite ingredient and click it onto the disc holder. Performance has been tested extensively to provide the best slicing and shredding results.

Powerful processing

650 W

This Philips Food Processor offers a powerful motor providing power and control to prepare all your favorite recipes.

Up to 5 portions in one go



The generous 2.1L bowl (1.5 L working capacity) enables you to blend up to 5 portions of soup in one go.

Dishwasher safe accessories



All accessory parts of your Philips food processor can be put on the top rack of your dishwasher for easy cleaning.

Emulsifying tool



The perfect tool for whipping, whisking or emulsifying eggs or whipped cream. For best volume increase and fluffiness, use the low speed setting. Creating delicious desserts or mayonnaise has never been easier!

PowerChop technology



PowerChop

PowerChop technology is a combination of blade shape, cutting angle and inner bowl that provides a superior chopping result in both soft and hard ingredients. It is also perfect for making purées and mixing your cake batters!



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Accessories

Included: Blade unit S-blade, Chopping knife, Emulsifying tool, Fine shredding tool, Fine slicing tool, Granulating tool

General specifications

Number of slicing disks: 3

Number of speed settings: 2 + pulse

Product features: Integrated cord storage, Non-slip feet, Pulse

Technical specifications

Power: 650 W

Voltage: 220-240 V

Frequency: 50/60 Hz

Capacity bowl: 2 L

Capacity jar: 1.75 L

Cord length: 1.0 m

RPM blender (max): 21000 rpm

RPM bowl (max): 1900 rpm

Working capacity bowl: 1.5 L

Working capacity jar: 1.0 L

Design

Color: White

Finishing

Material accessories: Stainless steel

Material jar: Plastic SAN

Material of main body: Plastic ABS

Service

2-year worldwide guarantee

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH):

244x244x377 mm

Accessories included

Fine shredding disk

