

PHILIPS

Food processor

700 W

Compact 2 in 1 setup

3.4 L bowl

HR7771/00



Great cooking, effortlessly

With color codes for easy cooking

The Philips Food Processor is the multifunctional answer to all your kitchen problems. The color coded accessories and speed settings help you to match the color of the speed with the color of the accessory for optimized results.

Powerful precision

- 2 speed settings for optimal speed/accessory combination
- Pulse button for maximum control of end results
- 700W motor to handle large quantities and heavy kneading

Effortlessly easy

- Color coded accessory and speed combinations
- 5 accessories to easily perform 25+ functions
- XL feeding tube takes whole fruits or vegetables
- Up to 7 portions in 1 go with the XL bowl
- Form fitting couplings and tools for easy assembly

Reliably durable

- Dishwasher safe accessories
- Break resistant jar withstands intensive use
- Sturdy base stands stable, even with heavy kneading

Highlights

Color coded accessories/speeds



Match the color of the speed with the color of the accessory for optimized results.

25+ functions



The - dishwasher safe - accessories are a kneading tool for mixing batter and for heavy kneading. A stainless steel chopping knife to prepare meat and vegetables. Two metal disks to handle medium and fine shredding and grating. Break resistant blender of 1.5 L for blending, crushing and stirring different ingredients. An emulsifying disk to prepare food like whipped cream and mayonnaise.

XL 3.4 L bowl



The XL bowl allows for maximum volumes to be processed in one go: capacity for 2 l soup, 1.7 kg dough, 7 eggwhites.

XL feeding tube



The XL feeding tube takes whole fruits and vegetables so you don't need to pre-cut them anymore.

700W motor + 2 speeds + pulse

With the powerful 700W motor plus 2 speed settings and pulse button you can pick the right speed.

Specifications

Technical specifications

Voltage: 220-240 V
Frequency: 50-60 Hz
Speeds: 2+ pulse
Cord length: 120 cm
Bowl capacity dry: 3.4 L
Safety: Lid & bowl detection, mechanical 1.5 sec brake
Blender jar capacity: 1.5 L
Bowl working capacity dough: 1700 g
Bowl working capacity flour: 1000 g
Bowl capacity liquid: 2 L

Accessories

Number of inserts/discs: 2
Kneading tool: For (heavy) kneading, mixing dough, batter
Emulsifying disk: For whipping, whisking and emulsifying application
Stainless steel chopping knife: chopping, Beating, creaming, crumbling, cutting, folding in, mashing, mincing
Break resistant blender: blending, crushing, foaming, grinding, pureeing, homogenizing, liquidizing, milling, shaking, stirring

Design specifications

Housing: ABS
Emulsifying disc: PP
Speed knob: ABS
Function buttons: Pulse
Pusher, inner pusher: ABS, SAN
Disks, chopping blade: Stainless steel
Color(s): Shiny white, dark grey accents, elegant color coding
Bowl including lid and blender: SAN

General specifications

Non-slip feet
Integrated cord storage

Country of origin

China

