

# PHILIPS

Food processor

700 W

Compact 2 in 1 setup

3.4 L bowl

HR7771/53



## Great cooking, effortlessly

### With colour codes for easy cooking

The Philips Food Processor is the multifunctional answer to all your kitchen problems. The colour coded accessories and speed settings help you to match the colour of the speed with the colour of the accessory for optimised results.

#### **Powerful precision**

- 700 Watt motor to handle large quantities and heavy kneading
- 2 speed settings for optimal speed/accessory combination
- Pulse button for maximum control of end results

#### **Effortlessly easy**

- Colour-coded accessory and speed combinations
- 5 accessories to easily perform 25+ functions
- XL feeding tube takes whole items of fruit or vegetables
- Up to 7 portions in 1 go with the XL bowl
- Form-fitting couplings and tools for easy assembly

#### **Reliably durable**

- Dishwasher-safe accessories
- Break-resistant jar withstands intensive use
- Sturdy base stands stable, even with heavy kneading

# Highlights

## Colour-coded accessories/speeds



Match the colour of the speed with the colour of the accessory for optimised results.

## 25+ functions

The dishwasher safe accessories include a kneading tool for mixing batter and for heavy kneading, a stainless steel chopping knife to prepare meat and vegetables and two metal discs to handle medium and fine shredding and grating. Break-resistant blender of 1.5 l for blending, crushing and stirring different ingredients. An emulsifying disc to prepare food like whipped cream and mayonnaise.

## 2 speed settings

With the powerful 700 W motor plus 2 speed settings and pulse button you can pick the right speed

## 700 W motor + 3 speeds + pulse

With the powerful 700 W motor plus 3 speed settings and pulse button you can pick the right speed

## Break resistant jar

Break-resistant jar withstands intensive use

## Dishwasher-safe accessories



Dishwasher-safe accessories

## Form-fitting couplings

Form-fitting couplings and tools for easy assembly

## Pulse button

Pulse button for maximum control of end results

## Sturdy base

The sturdy base comes with suction feet to ensure it does not move, even when you use it for heavy applications like kneading dough.

## XL 3.4 L bowl



The XL bowl allows for maximum volumes to be processed in one go: capacity for 2 l soup, 1.7 kg dough, 7 egg whites.

## XL feeding tube



The XL feeding tube takes whole items of fruits and vegetables so you don't need to pre-cut them any more.

# Specifications

## Technical specifications

**Voltage:** 220–240 V

**Frequency:** 50–60 Hz

**Speeds:** 2+ pulse

**Cord length:** 120 cm

**Bowl capacity dry:** 3.4 l

**Safety:** Lid and bowl detection, mechanical 1.5 sec brake

**Blender jar capacity:** 1.5 l

**Bowl working capacity dough:** 1700 g

**Bowl working capacity flour:** 1000 g

**Bowl capacity liquid:** 2 l

## Accessories

**Number of inserts/discs:** 2

**Kneading tool:** For (heavy) kneading, mixing dough, batter

**Emulsifying disc:** For whipping, whisking and emulsifying application

**Stainless steel chopping knife:** chopping, Beating, creaming, crumbling, cutting, folding in, mashing, mincing

**Break-resistant blender:** blending, crushing, foaming, grinding, pureeing, homogenising, liquidising, milling, shaking, stirring

## Design specifications

**Housing:** ABS

**Emulsifying disc:** PP

**Speed knob:** ABS

**Function buttons:** Pulse

**Pusher, inner pusher:** ABS, SAN

**Disks, chopping blade:** Stainless steel

**Colour(s):** Shiny white, dark grey accents, elegant colour coding

**Bowl including lid and blender:** SAN

## General specifications

**Non-slip feet**

**Integrated cord storage**

## Country of origin

China

