

PHILIPS

Food processor

700 W

Compact 2 in 1 setup

3.4 L bowl



HR7772/00



Great cooking, effortlessly

With colour codes for easy cooking

The Philips Food Processor is the multifunctional answer to all your kitchen problems. The colour coded accessories and speed settings help you to match the colour of the speed with the colour of the accessory for optimised results.

Powerful precision

- 700 Watt motor to handle large quantities and heavy kneading
- 3 speed settings for optimal speed/accessory combination
- Pulse button for maximum control of end results

Effortlessly easy

- Colour-coded accessory and speed combinations
- 6 accessories to easily perform 30+ functions
- XL feeding tube takes whole items of fruit or vegetables
- Up to 7 portions in 1 go with the XL bowl
- Form-fitting couplings and tools for easy assembly

Reliably durable

- Dishwasher-safe accessories
- Break-resistant jar withstands intensive use
- Sturdy base stands stable, even with heavy kneading

Highlights

Colour-coded accessories/speeds



Match the colour of the speed with the colour of the accessory for optimised results.

30+ functions



The accessories, which are dishwasher safe, are: a kneading tool for mixing batter and for heavy kneading; a stainless steel chopping knife to prepare meat and vegetables; two metal discs to handle medium and fine shredding and grating; a break-resistant 1.5 l blender for blending, crushing and stirring different ingredients; an emulsifying disc to prepare food like whipped cream and mayonnaise.

700 W motor + 3 speeds + pulse

With the powerful 700 W motor plus 3 speed settings and pulse button you can pick the right speed

XL 3.4 L bowl



The XL bowl allows for maximum volumes to be processed in one go: capacity for 2 l soup, 1.7 kg dough, 7 egg whites.

XL feeding tube



The XL feeding tube takes whole items of fruits and vegetables so you don't need to pre-cut them any more.

Specifications

Technical specifications

Voltage: 220–240 V
Frequency: 50–60 Hz
Speeds: 3+ pulse
Cord length: 120 cm
Bowl capacity dry: 3.4 l
Safety: Lid and bowl detection, mechanical 1.5 sec brake
Blender jar capacity: 1.5 l
Bowl working capacity dough: 1700 g
Bowl working capacity flour: 1000 g
Bowl capacity liquid: 2 l

Accessories

Number of inserts/discs: 2
Kneading tool: For (heavy) kneading, mixing dough, batter
Citrus press: For pressing of citrus fruits
Balloon beater: For whipping, whisking, mixing and emulsifying
Stainless steel chopping knife: chopping, Beating, creaming, crumbling, cutting, folding in, mashing, mincing
Break-resistant blender: blending, crushing, foaming, grinding, pureeing, homogenising, liquidising, milling, shaking, stirring

Design specifications

Housing: ABS
Speed knob: ABS
Function buttons: Pulse
Pusher, inner pusher: ABS, SAN
Knife holder, balloon beater: POM
Disks, chopping blade: Stainless steel
Kneading tool, citrus press: PP
Colour(s): Shiny white, dark grey accents, elegant colour coding
Bowl including lid and blender: SAN

General specifications

Non-slip feet
Integrated cord storage

Country of origin

China

