

PHILIPS

Food processor

700 W

Compact 2 in 1 setup

3.4 L bowl

HR7772/50



Great cooking, effortlessly

Food processor with color code cooking

The Philips Food Processor is the multifunctional answer to all your kitchen problems. The color coded accessories and speed settings help you to match the color of the speed with the color of the accessory for optimized results.

Powerful precision

- 700 Watt motor to handle large quantities and heavy kneading
- 3 speed settings for optimal speed/accessory combination
- Pulse button for maximum control of end results

Effortlessly easy

- 7 accessories to easily perform 30+ functions
- Color coded accessory and speed combinations
- XL feeding tube takes whole fruits or vegetables
- Up to 7 portions in 1 go with the XL bowl
- Easy cleaning after use

Reliably durable

- Dishwasher safe accessories
- Break resistant jar withstands intensive use
- Sturdy base stands stable, even with heavy kneading

Highlights

Color coded accessories/speeds



Match the color of the speed with the color of the accessory for optimized results.

30+ functions



The – dishwasher safe – accessories are a kneading tool for mixing batter and for heavy kneading. A stainless steel chopping knife to prepare meat and vegetables. Two metal disks to handle medium and fine shredding and grating. Break resistant blender of 1.5l for blending, crushing up to stirring different ingredients. A citrus press for pressing citrus fruits. And a balloon beater for whipping and whisking and handling light batter.

700 W motor + 3 speeds + pulse

With the powerful 700W motor plus 3 speed settings and pulse button you can pick the right speed

XL 3.4 L bowl




The XL bowl allows for maximum volumes to be processed in one go: capacity for 2 l soup, 1.7 kg dough, 7 eggwhites.

XL feeding tube



The XL feeding tube takes whole fruits and vegetables so you don't need to pre-cut them anymore.

Easy cleaning after use



Cleaning your food processor after use is easy. Simply pour some lukewarm water and washing-up liquid into the blender or bowl and press the Pulse button for a few seconds.

Specifications

Technical specifications

Voltage: 220–240 V
Frequency: 50–60 Hz
Speeds: 3+ pulse
Cord length: 120 cm
Bowl capacity dry: 3.4 l
Safety: Lid & bowl detection, mechanical 1.5 sec brake
Blender jar capacity: 1.5 l
Bowl working capacity dough: 1700 g
Bowl working capacity flour: 1000 g
Bowl capacity liquid: 2 l

Accessories

Number of inserts/discs: 2
Kneading tool: For (heavy) kneading, mixing dough, batter
Citrus press: For pressing of citrus fruits
Balloon beater: For whipping, whisking, mixing and emulsifying
Stainless steel chopping knife: chopping, Beating, creaming, crumbling, cutting, folding in, mashing, mincing
Break resistant blender: blending, crushing, foaming, grinding, pureeing, homogenizing, liquidizing, milling, shaking, stirring

Design specifications

Housing: ABS
Speed knob: ABS
Function buttons: Pulse
Pusher, inner pusher: ABS, SAN
Knife holder, balloon beater: POM
Disks, chopping blade: Stainless steel
Kneading tool, citrus press: PP
Color(s): Shiny white, dark grey accents, elegant color coding
Bowl including lid and blender: SAN

General specifications

Non-slip feet
Integrated cord storage

Country of origin

China

