

Food processor

Aluminium Collection

1000 W

Compact 3-in-1 setup

3.4 L bowl



HR7775/00



Effortless excellence

Food processor with the fastest juicing accessory

This Philips food processor HR7775/00 has some of the most advanced technologies. Its versatility is ensured by 10 accessories that easily perform 30+ functions. Additionally this Food Processor offers you a professional juicing accessory.

With professional juicing accessory

- Patented micromesh filter gets out more juice
- Up to 200% faster juicing compared with other food processor juicers

Powerful precision

- 1000 W motor
- Ice and pulse functions for chopping and crushing
- Adjustable blade for slices between 1–7 mm

Effortlessly easy

- 10 accessories to easily perform 30+ functions
- XL feeding tube takes whole items of fruit or vegetables
- Up to 7 portions in 1 go with the XL bowl

Stylishly compact

- Stylish design to fit your kitchen
- Compact 3-in-1 setup saves countertop space

Highlights

Up to 200% faster juicing



This food processor is the first to offer you a professional juicing accessory. Thanks to its extra large feeding tube and patented large metal mesh filter, it can juice up to 200% faster compared with other food processor juicers. And thanks to its ergonomic design, it is quicker to clean and store.

Patented micromesh filter

The patented micromesh filter made of stainless steel squeezes every drop to give you more juice.

30+ functions



The dishwasher-safe accessories are: a kneading tool for mixing batter and for heavy kneading; A stainless steel chopping knife to prepare meat and vegetables; Two metal disks to handle medium and fine shredding and grating; Break-resistant blender of 1.5 L for blending, crushing and stirring different ingredients; A citrus press for pressing citrus fruits; And a balloon beater for whipping and whisking and handling light batter.

Adjustable slicing blade

With the adjustable slicing blade, you can make slices as thin as 1 mm and up to 7 mm thick.

1000 W motor

With the powerful 1000 W motor of this Philips food processor you can adjust speed precisely to get desired results.

XL feeding tube



The XL feeding tube takes whole items of fruits and vegetables so you don't need to pre-cut them any more.

XL 3.4 L bowl



The XL bowl allows for maximum volumes to be processed in one go: capacity for 2 l soup, 1.7 kg dough, 7 egg whites.

Compact 3-in-1 setup

Compact 3-in-1 setup fits juice extractor, blender or bowl so uses up a minimum of space on your countertop.

Stylish design

Stylish and compact design looks great in every kitchen and takes up little space on your kitchen counter.

Specifications

Technical specifications

Voltage: 220–240 V
Bowl capacity dry: 3.4 l
Bowl volume capacity liquid: 2.0 l
Bowl working capacity dough: 1700 g
Bowl working capacity flour: 1000 g
Blender jar capacity: 1.5 l
Safety: Lid and bowl detection, mechanical 1.5 sec brake
Speeds: VarioSpeed
Juice extractor capacity: 1.5 l
Cord length: 120 cm

Accessories

Number of inserts/discs: 4
Reversible shredding disk: For medium/fine shredding
Adjustable slicing disk: For 1–7 mm slices of fruit and vegetables
Julienne/French fry disk: For julienne strips or French fries
Granulating disc: For grating potatoes or cheese
Juice extractor: For juicing apples, carrots etc
Spatula:
Citrus press: For pressing of citrus fruits
Kneading tool: For kneading, heavy kneading, mixing dough, batter
Stainless steel chopping knife: chopping, Beating, creaming, crumbling, cutting, folding in, mashing
Balloon beater: For whipping, whisking, mixing and emulsifying
Break-resistant blender: blending, crushing, foaming, grinding, pureeing, homogenising, liquidising, milling, shaking, stirring

Design specifications

Housing: ABS + brushed aluminium
Juice extractor: Stainless steel, ABS, SAN, POM
Knife holder, balloon beater: POM
Disks, chopping blade: Stainless steel
Speed knob: Brushed aluminium
Kneading tool, citrus press: PP
Function buttons: ice, pulse
Bowl including lid and blender: SAN
Pusher, inner pusher: ABS, SAN
Colour(s): Aluminium and charcoal grey

General specifications

Integrated cord storage
Non-slip feet

Country of origin

China

