

PHILIPS

Food processor

Avance Collection

1300W

Compact 4 in 1 setup

3.4 L bowl

One touch auto buttons

HR7777/00



Maximum variety of recipes, minimum effort

Create home made breads, cakes, drinks and more

This Philips Avance collection Food Processor is the versatile solution for your kitchen needs. With its new innovative metal kneading hook, powerful 1300 W motor and one touch auto button for dough, making bread has never been so easy.

Baking homemade breads and cakes is now so simple

- Double metal balloon beater for cream and egg whites
- Metal kneading hook for perfect bread dough
- Blade unit for mixing and blending cake batters

Confidently control power and speed settings

- PowerChop technology for superior chopping performance
- One touch auto buttons for bread dough, whipping and ice

Easy processing and effortless cleaning

- XXL 18cm discs for faster execution of all ingredients
- Dishwasher safe accessories
- Large-capacity bowl and blender jar for the whole family

Carefully selected accessories for best results

- Reversible disc for shredding (fine and coarse)
- Citrus press and 2 glass centrifugal juicer



asimpleswitch.com

Highlights

Double metal balloon beater



The double metal balloon beater together with the one touch auto button creates fluffy egg whites (up to 600% volume increase) and perfectly whipped cream (up to 200% volume increase). Creating delicious desserts has never been easier!

Innovative metal kneading hook



Together with the strong motor, this metal kneading hook quickly forms a dough ball from your ingredients. Once the dough is formed, the innovative kneading hook works the dough with the right force and power to enable you to make the tastiest bread.

Blade unit

Blade unit for mixing and blending cake batters

PowerChop technology



PowerChop

PowerChop technology is a combination of blade shape, cutting angle and inner bowl that provides a superior chopping result in both soft and hard ingredients. It is also perfect for making purées and mixing your cake batters!

One touch auto buttons



In addition to the manual 12 speed + pulse control, this Avance Food Processor comes with 3 one touch auto buttons. To select them, simply turn the control dial to the "ON" position and press the one touch auto button. The motor then automatically sets the right speed and auto pulse functions for the best results.

XXL Discs for faster execution

Thanks to the XXL discs (18cm), the Philips food processor will provide you a faster performance saving you time and effort while cooking.

Dishwasher safe accessories



All Philips Food Processor accessories included in your box are dishwasher safe.

XL bowl and blender jar



The extra-large 3.4-liter bowl has a working capacity of 2 liters to handle up to 7 servings of soup, 7 eggs whites or 1.7 kg of dough. A 2.2-liter blender jar handles 1.5 liters of ingredients for up to 5 smoothie portions in one go.

Reversible disc for shredding



The reversible shredding disc (fine and coarse) is suitable for all types of vegetables.

2 glass centrifugal juicer

This 2 glass centrifugal juicer accessory is ideal for extracting fresh juice from all types of fruit such as apples, carrots, watermelon and grapes.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

General specifications

Functions: 30+

RPM-Blender&Grinder Mill(min): Up to 6500 rpm

RPM-Bowl(min): Up to 575 rpm

Bowl max working capacity.: 1000g (Flour)

3 preset buttons

Adjustable slicing disks: 1-7 mm

Number of speed settings: 12 + pulse

Product features: Dishwasher safe, Integrated cord storage, Non-slip feet, On/off switch, Pulse

Accessories

Included: Blade unit S-blade, Citrus press, Coarse shredding tool, Double balloon beater, Jar, Kneading tool, Reversible disc, Spatula

Design specifications

Citrus press: PP

Discs, chopping knife: Stainless steel

Kneading tool: POM and metal

Pusher: ABS

Speed knob: ABS

Knife holder, balloon beater: POM

S-blade, knife, metal discs: Stainless steel

Technical specifications

Blender jar max capacity: 2.2L

Blender jar working capacity: 1.5L

Cord length: 1.2 m

Frequency: 50/60 Hz

Power: 1300 W

Safety: Lid & bowl detection, mechanical 1.5 sec brake

Voltage: 220-240 V

FP Bowl efficient capacity: 2 L

FP Bowl Max capacity: 3.4 L

RPM blender (max): 20000 rpm

RPM bowl (max): 1700 rpm

Finishing

Material jar: SAN

Material of main body: Stainless steel

Weight and dimensions

Dimensions of product (LxWxH):

289x254x436 mm

