

PHILIPS

Food processor

Avance Collection

1300W

Compact 4 in 1 setup

3.4 L bowl

One touch auto buttons



HR7778/01



Maximum variety of recipes, minimum effort

Create home made breads, cakes, drinks and more

This Philips Avance collection Food Processor is the versatile solution for your kitchen needs. With its new innovative metal kneading hook, powerful 1300 W motor and one touch auto button for dough, making bread has never been so easy.

Baking homemade breads and cakes is now so simple

- Double metal balloon beater for cream and egg whites
- Metal kneading hook for perfect bread dough
- Blade unit for mixing and blending cake batters

Confidently control power and speed settings

- PowerChop technology for superior chopping performance
- One touch auto buttons for bread dough, whipping and ice

Easy processing and effortless cleaning

- XXL 18cm discs for faster execution of all ingredients
- Dishwasher safe accessories
- 3.4 L bowl and 2.2 L blender jar for family sized portions

Carefully selected accessories for best results

- Stainless steel discs to slice, shred, granulate & cut fries
- Citrus press and 6 glass centrifugal juicer with metal mesh



asimpleswitch.com

Highlights

Double metal balloon beater



The double metal balloon beater together with the one touch auto button creates fluffy egg whites (up to 600% volume increase) and perfectly whipped cream (up to 200% volume increase). Creating delicious desserts has never been easier!

Innovative metal kneading hook



Together with the strong motor, this metal kneading hook quickly forms a dough ball from your ingredients. Once the dough is formed, the innovative kneading hook works the dough with the right force and power to enable you to make the tastiest bread.

Blade unit

Blade unit for mixing and blending cake batters

PowerChop technology



PowerChop technology is a combination of blade shape, cutting angle and inner bowl that provides a superior chopping result in both soft and hard ingredients. It is also perfect for making purées and mixing your cake batters!

One touch auto buttons



In addition to the manual 12 speed + pulse control, this Avance Food Processor comes with 3 one touch auto buttons. To select them, simply turn the control dial to the "ON" position and press the one touch auto button. The motor then automatically sets the right speed and auto pulse functions for the best results.

XXL Discs for faster execution

Thanks to the XXL discs (18cm), the Philips food processor will provide you a faster performance saving you time and effort while cooking.

Dishwasher safe accessories



All Philips Food Processor accessories included in your box are dishwasher safe.

3.4 L bowl and 2.2 L blender



The XL bowl allows for maximum volumes to be processed in one go, for example up to 7 portions of soup, 7 eggs whites, 1.7 kgs of dough. In addition, the 2.2 L blender easily creates up to 5 smoothie portions in one go.

4 stainless steel discs



This food processor comes with an additional range of 4 stainless steel discs: 1 reversible shredding disc (fine and coarse) for all types of vegetables, 1 granulating disc for potatoes or cheese, 1 julienne disc for thin vegetable strips and 1 French Fry disc for thick potato strips.

6 glass centrifugal juicer



This food processor includes a professional juicing accessory. Thanks to its extra large feeding tube and patented large metal mesh filter, it can juice up to 200% faster compared with other food processor juicers. The patented micromesh filter made of stainless steel squeezes every drop to give you more juice. And thanks to its ergonomic design, it is quicker to clean and store.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Accessories

Adjustable slicing disc: 1-7 mm

Citrus press

Double balloon beater

Juice extractor: 6 glass metal mesh centrifugal juicer

Metal kneading hook

Spatula

Stainless steel S-blade

Blender Jar

Reversible disc: slicing/shredding(coarse/fine)

Design specifications

Bowl including lid: SAN

Citrus press: PP

Discs, chopping knife: Stainless steel

Housing: Stainless steel

Kneading tool: POM and metal

Pusher: ABS

Speed knob: ABS

Knife holder, balloon beater: POM

S-blade, knife, metal discs: Stainless steel

General specifications

Speeds: 12 + pulse

Functions: 30+

Cord length: 1 m

3 preset buttons

Integrated cord storage

Non-slip feet

RPM-Blender&Grinder Mill(max): Up to 20000 rpm

RPM-Blender&Grinder Mill(min): Up to 6500 rpm

RPM-Bowl(max): Up to 1700 rpm

RPM-Bowl(min): Up to 575 rpm

Bowl max working capacity: 2.4L (dry/liquid)

Bowl max working capacity: 1000g (Flour)

Bowl capacity: 3.4 L

Blender jar working capacity: 1.5L

Main unit with bowl: 289x254x436 mm

blender jar capacity: 2.2 L

Technical specifications

Power: 1300 W

Frequency: 50/60 Hz

Voltage: 220-240 V

Safety: Lid & bowl detection, mechanical 1.5 sec brake

Cord length: 1.2 m

