

PHILIPS

NIVEA

FOR MEN

NIVEA FOR MEN shaver

with refill and charge stand

HS8060/24



Smooth shave, healthy skin

Conditioner Dispensing System

NIVEA FOR MEN shaving conditioner is dispensed directly onto your skin for a moisturising and soothing shave. The formula is enriched with vitamins and chamomile to condition your skin and support a healthy look

Moisturising and soothing shave

- NIVEA FOR MEN conditioner dispensing system

Easy shaving conditioner refill

- Integrated cartridge refill system

Skin protection system

- Flex Tracker system

Superior gliding

- Glide rings

Automatic refill and charge

- Refill and charge stand

Highlights

Conditioner dispensing system




NIVEA FOR MEN moisturising shaving conditioner is dispensed directly onto your skin

Integrated cartridge refill system



Simply pump the NIVEA FOR MEN shaving conditioner from the refill can directly into the Philips NIVEA FOR MEN shaver.

Flex Tracker system



The Flex Tracker automatically tracks the curves of your face and helps to protect against skin irritation.

Glide rings



The shaving heads have unique glide rings to help the shaver move smoothly over your face.

Refill and charge stand



Automatically refills shaver with NIVEA FOR MEN conditioner and keeps shaver fully charged at all times.

Wet use



Use the shaver in the shower to save time and give yourself the fresh sensation of wet shaving.

Specifications

Shaving Performance

Shaving system: Lift & Cut technology
Contour following: Flex Tracker system
SkinComfort: NIVEA FOR MEN conditioner dispensing system, Glide rings
Styling: Skin-friendly precision trimmer

Ease of use

Display: Battery full indicator, Battery low indicator, Charge indicator, Travel lock
Charging: Rechargeable, Refill and charge, Quick charge, Cordless
Charging: 1.5 hours
Wet and Dry: Shower use
Shaving time: 13 days
Cleaning: Washable

Design

Finishing: Varnish

Accessories

Creams and Lotions: 75 ml shaving conditioner refill
Stand: Charging stand, Refill and charge stand
Pouch: Soft pouch
Maintenance: Protective cap

Power

Run time: 40 min

