


PHILIPS

Air humidifier

Safe & clean

NanoCloud technology

HU4801/30



Healthy air, always

Smart humidification with easy cleaning

Philips air humidifier fights dry air with maximum efficiency and hygiene. It evenly distributes humidified air throughout the room and has 99% less bacterial spreading compared with ultra sonic humidifiers. No white dust and wetting floors

Healthy Air

- Hygienically safer, and no white dust and no wet floors
- Evenly distributes humidified air throughout the room

Always

- Auto shut down when humidifier runs out of water

Simplicity

- Choose between silent and standard humidification
- Easy-fill tank
- Minimalist design gives you best-in-class cleanability



asimpleswitch.com

Highlights

Advanced evaporation system

This Philips Air humidifier offers a three-stage advanced evaporation system. Stage 1, the absorbent filter on the humidifier catches big particles such as human/pet hair and dust when drawing in the dry air. Stage 2, the advanced evaporation technology retains all bacteria, viruses and calcium from the water ensuring that only pure water humidifies the dry air. Stage 3, healthy air gets blown out of the humidifier at a constant speed, delivering comfortable, pure air humidification in your home.

Comfortable humidification



Evenly distributes humidified air throughout the room. Breathe and sleep better at home with healthy humidified air

Dual humidification speed



Choose between silent and standard humidification to allow maximum flexibility.

Best-in-class cleanability



Cleaning humidifiers inside and out – especially the water tank – has never been easier

Easy-to-fill tank



Fill with a jar or bring the water tank to the tap. The 'max' indicator clearly shows how far to fill the tank. When the tank is empty, the humidifier automatically shuts off and the display indicates a re-fill is needed.

Healthy ari protect lock

When the water tank is empty and needs to be refilled, the healthy air protect lock shuts off the humidifier.

Specifications

Design and finishing

Color(s): White, light green

Performance

Humidification rate: 200 ml/h

Technical specifications

Effective area: 25 m²

Sound level: 26 dB(A)

Voltage: 220-240 V

Operation time: 8 hour(s)

Water tank capacity: 2 L

Country of origin

Made in: China

Replacement

Humidification filter: Replace HU4102 once every 3 working months

Weight and dimensions

Dimensions of product (LxWxH): 249 x 249 x 339 mm



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO₂ emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.