

PHILIPS

sonicare

Sonic electric
toothbrush

DailyClean

1 mode

1 brush head



HX3415/06



Clinically proven to provide superior cleaning * Gently removes stains for naturally whiter teeth

Designed to be the perfect toothbrush to transition from your manual toothbrush. Until now, it feels like you've never brushed your teeth before.

Innovative technology

- Philips Sonicare's advanced sonic technology

Designed around you

- Timers encourage thorough 2 minutes of brushing
- A great way to get used to your new toothbrush

Optimize your brushing

- Battery life
- Click-on brush head system

Highlights

The only true sonic technology



Philips Sonicare's advanced sonic technology pulses water between teeth, and its brush strokes break up plaque and sweep it away for an exceptional daily clean.

QuadPacer and Smartimer



It takes just 2 minutes to thoroughly brush your teeth. Our QuadPacer lets you know when you've spent the optimal amount of time on each section of your mouth while our Smartimer signals when your total time is up. Together they help you reach your recommended brushing time, every time.

Easy-start program



Starting something new can take getting used to. That's why our easy-start program gives you the option of a gradual, gentle increase in brushing power the first 14 times you use your new toothbrush.

Battery life



Lasts up to 14 days between charges.

Click-on brush head system



This brush head clicks on and off your brush handle for a secure fit and easy maintenance and cleaning. It fits Philips Sonicare toothbrush PowerUp Battery, Essence+/Elite+/CleanCare+ handles.

Specifications

Modes

Clean: For exceptional everyday clean

Items included

Handle: 1 DailyClean

Brush heads: 1 S Sensitive standard

Charger: 1

Design and finishing

Color: Pink

Cleaning performance

Speed: Up to 31000 brush movement/min

Timer: Smartimer and Quadpacer

Ease of use

Brush head system: Easy click-on brush heads

Handle: Ergonomic design

Technical specifications

Battery: Rechargeable

Battery type: NiMH

Operating time (full to empty): Up to 14 days

Power

Voltage: 110-220 V

Service

Warranty: 2-year limited warranty

