

# PHILIPS

## sonicare

Sonic electric  
toothbrush

ProtectiveClean  
4300

Built-in pressure sensor

1 cleaning mode

1 x BrushSync feature



HX6800/03



## Cleaner teeth. Gently does it.

Remove up to 7 x more plaque than a manual

Feel the difference of a gentle clean with our Pressure Sensor while removing up to 7 x more plaque than a manual toothbrush

### Proven to improve oral health

- Up to 7x more plaque removal than a manual toothbrush
- Safe and gentle on sensitive areas, orthodontics and dental work

### Innovative technology

- Lets you know when you're pressing too hard
- Philips Sonicare's advanced sonic technology
- Connects smart brush handle and smart brush heads

### Designed around you

- A great way to get used to your new toothbrush
- Encouragement to brush thoroughly
- Always know when to replace your brush heads
- Makes traveling easier for you


# Highlights

## Say goodbye to plaque



Densely-packed, high-quality bristles remove up to 7 x more plaque than a manual toothbrush. And the specially curved power tip makes reaching the teeth at the back of your mouth a breeze.

## Too much pressure?



You may not notice if you're brushing too hard, but your toothbrush will. If you start taking it out on your gums, the toothbrush will make a pulsing sound as a reminder to ease off on the pressure.

## Easy-start programme



Starting something new can take getting used to. That's why our easy-start programme gives you the option of a gradual, gentle increase in brushing power the first 14 times you use your new toothbrush.

## Safe and gentle




You can be sure of a safe brushing experience: our sonic technology is suitable for use with braces, fillings, crowns and veneers, and helps prevent cavities and improve gum health.

## BrushSync technology



A microchip-enabled technology that detects and synchronises the smart brush head with the smart handle. The smart handle and smart brush head pair is a powerful combination that enables Smart replacement reminders.

## Helpful timers



Our QuadPacer lets you know when you've spent just the right amount of time cleaning each part of your mouth, while our Smartimer tells you when you've brushed for the recommended two minutes.

## The only true sonic technology



Philips Sonicare's advanced sonic technology pulses water between your teeth, and its brush strokes break plaque up and sweep it away for an exceptional daily clean.

## BrushSync replacement reminder



All brush heads wear out over time. But our BrushSync technology tracks how long you've been using your brush head for, and how hard you've been brushing. When it's time to replace it, a light on your handle and a short beep will let you know. That way, you can be sure your brush head is doing a good job.

## Handy travel case and charger



Our premium travel case lets you store your toothbrush hygienically, while our compact charging base keeps you topped up when you're on the go. You do get two weeks of regular use from a single full charge, but the charger's just the ticket for longer trips.

# Specifications

## Modes

**Clean:** For exceptional everyday cleaning

**2 intensities:** Low, High

## Items included

**Handle:** 1 ProtectiveClean

**Brush heads:** 1 C2 Optimal Plaque Defence

**Travel case:** 1

**Charger:** 1

## Design and finishing

**Colour:** Black Grey

## Cleaning performance

**Speed:** Up to 62,000 brush movements/min

**Performance:** Removes up to 7x more plaque\*

**Health benefits:** Helps reduce cavities

**Pressure feedback:** Vibrates handle to alert user

**Timer:** SmartTimer and Quadpacer

## Smart sensor technology

**Pressure sensor:** Alerts when brushing too hard

**BrushSync Replacement Reminder:** Always know when to, replace brush heads

## Ease of use

**Handle compatibility:** Easy click-on brush heads

**Battery indicator:** Light shows battery status

**Handle:** Slim ergonomic design

**Brushing time:** Up to 2 weeks

## Technical specifications

**Battery:** Rechargeable

**Battery type:** Lithium ION

**Operating time (full to empty):** Up to 2 weeks

## Power

**Voltage:** 110-220 V

## Service

**Warranty:** 2-year limited warranty

