

PHILIPS

sonicare

Sonic electric
toothbrush

ProtectiveClean
4300

Built-in pressure sensor

1 cleaning mode

1 x BrushSync feature



HX6848/92



Whiter teeth. Gently does it.

Whitens teeth in just 1 week.

Feel the difference of a gentle clean with our Pressure Sensor while whitening your teeth in 1 week.

Proven to improve oral health

- Whitens teeth in just one week

Innovative technology

- Improves gingival health in just 2 weeks
- Philips Sonicare's advanced sonic technology
- A gentle nudge to go nice and easy
- Patients get the most from their brush heads
- Connects smart brush handle and smart brush heads

Designed around your patient

- A great way for patients to get used to their toothbrush
- Encouragement to brush thoroughly

Improves patients' oral health

- Fillings, crowns, or sensitive areas? Not to worry.


Highlights

Naturally whiter teeth



Click on the W2 Optimal White brush head to remove surface stains and reveal a whiter smile. With its densely packed central stain-removal bristles, it's clinically proven to whiten teeth in just one week.

Improves gingival health



The i InterCare brush head features extra-long, densely packed, high-quality bristles to target deep interdental plaque. It is clinically proven to reduce gingival bleeding and inflammation in just two weeks.

Too much pressure?



Patients may not notice if they are brushing too hard, but their toothbrush will. If patients start taking it out on their gums, the toothbrush will make a pulsing sound as a reminder to ease off on the pressure.

Safe and gentle




You can be sure of a safe brushing experience: our sonic technology is suitable for use with braces, fillings, crowns, and veneers, and helps prevent cavities and improve gum health.

Philips Sonicare technology




Philips Sonicare's advanced sonic technology pulses water between teeth, and its brush strokes break up plaque and sweep it away for an exceptional daily clean.

Smart replacement reminders



All brush heads wear out over time. But we've got that covered too: our smart brush-recognition technology tracks how long patients have been using their brush head for, and how hard they've been brushing. When it's time to replace it, a light on the handle lets them know. That way, they can be sure that their brush head is consistently doing a stellar job.

Helpful timers




Our QuadPacer lets patients know when they've spent just the right amount of time cleaning each part of their mouth, while our Smartimer tells them when they've brushed for the recommended two minutes.

BrushSync technology



A microchip-enabled technology that detects and synchronizes the smart brush head with the smart handle. The smart handle and smart brush head pair is a powerful combination that enables Smart replacement reminders.

Easy-start program



Starting something new can take getting used to. That's why our easy-start program gives patients the option of a gradual, gentle increase in brushing power the first 14 times they use their new toothbrush.

Specifications

Modes

Clean: For exceptional everyday clean

2 intensities: Low, High

Items included

Handle: 1 ProtectiveClean

Brush heads: 1 W2c Optimal White compact, 1
ic InterCare compact, 1 Sensitive standard

Charger: 1

Design and finishing

Color: White and Mid Blue

Cleaning performance

Speed: Up to 62000 brush movement/min

Health benefits: Improves gum health in only
two weeks, Helps reduce cavities

Pressure feedback: Vibrates handle to alert
user

Timer: SmarTimer and Quadpacer

Smart sensor technology

Pressure sensor: Alerts when brushing too
hard

BrushSync Replacement Reminder: Always
know when to, replace brush heads

Ease of use

Handle compatibility: Easy click-on brush
heads

Battery indicator: Light shows battery status

Handle: Slim ergonomic design

Brushing time: Up to 2 weeks

Technical specifications

Battery: Rechargeable

Battery type: Lithium ION

Operating time (full to empty): Up to 2 weeks

Power

Voltage: 110-220 V

Service

Warranty: 2-year limited warranty

